


SIGN	DATE	DESCRIPTION	APPROVER
△	9/17'10	How to order is changed	Runner
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	



Material:

- Item ① Terminal(housing): PA66 30% GF (UL94V-0)
- Item ② Contact pin of short: copper.tin plated

Electrical:

- Voltage rating: 160V
- Current rating: 5.5A
- Withstanding Voltage: 1.32 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ±10°C/5 Sec
- APPROVAL: 

cULus

KE xx 1 1 x 0 xxxx G

No. OF POLES

04: 2×2 POLES

06: 2×3 POLES

:

48: 2×24 POLES

COLOR

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

G: Pb<40000ppm

A00 0: "@" Mark

△ A00 A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

POLE		2×2	2×3	2×4	2×5	2×6	2×7	2×8	2×9	2×10	2×11	2×12
A		8.50	12.00	15.50	19.00	22.50	26.00	29.50	33.00	36.50	40.00	43.50
B		3.50	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50
Tol.		±0.15					±0.20					
POLE	2×13	2×14	2×15	2×16	2×17	2×18	2×19	2×20	2×21	2×22	2×23	2×24
A	47.00	50.50	54.00	57.50	61.00	64.50	68.00	71.50	75.00	78.50	82.00	85.50
B	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50
Tol.		±0.25					±0.30					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KE 3.5mm W/O Flange Series (Vertical) DIP type											
PART NO.	KExx11x0xxxxG				DWG NO.	8KE0010						
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.						Tolerance		
		Runner 2010.09.17	Runner 2010.04.12							UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30						
				SHEET: 01/01	REV: C	X.XX ±0.10						
						X° ±1°						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>KE041150A000G</u>	<u>KE061150A000G</u>	<u>KE081150A000G</u>	<u>KE101150A000G</u>	<u>KE121150A000G</u>	<u>KE141150A000G</u>
<u>KE161150A000G</u>	<u>KE181150A000G</u>	<u>KE201150A000G</u>	<u>KE221150A000G</u>	<u>KE241150A000G</u>	<u>KE261150A000G</u>
<u>KE281150A000G</u>	<u>KE301150A000G</u>	<u>KE321150A000G</u>	<u>KE341150A000G</u>	<u>KE361150A000G</u>	<u>KE381150A000G</u>
<u>KE401150A000G</u>	<u>KE421150A000G</u>	<u>KE441150A000G</u>	<u>KE461150A000G</u>	<u>KE481150A000G</u>	<u>KE081100A000G</u>