


Dimension A&B



DIM A	Nx5.0
DIM B	(N-1)x5.0

N=Number of contacts

Poles	A&B Tolerance
2P-4P	±0.15
5P-8P	±0.25
9P-16P	±0.35
17P-24P	±0.40



N=Number of contacts



SIGN	DATE	DESCRIPTION	APPROVER
△	3/22'06	Hole size changed from 0.5mm to 1.3mm	Tony
△	01/12'07	Soldering temperature changed from 245° to 250°	Tason
△	01/12'07	Part NO is Changed	Tason
△	08/28'08	Construction is change	Seamus
△	09/01'08	Operating temperature changed from -30°C/+105°C to -40°C/+115°C	Seamus
△	11/09'10	Add is " VDE "	Aaron

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing:Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass Ni plated
- Item 3 Wire guard solder pin:Brass Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

- △ Electrical cULus / VDE
- Voltage rating : 300VAC / 450V
 - Current rating : 20A / 24A
 - Wire range : 0.2-2.5mm²
 - Solid wire(AWG) : 12-30
 - Stranded wire(AWG) : 12-30
 - Torque : 3.5 Lb-In / 0.5 N.m
 - Screw: M3
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV / 2.5KV
 - △ ● Operating temperature: -40°C to +115°C
 - △ ● Soldering temperature: 250°C±10°C/5 Sec
 - Safety Approval:

△ VJ xx 01 x 2 xxxx G

No. of poles end
stackable design
02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

RoHS
Pb<40,000ppm
0000:"@ "Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VJ-5.0 Series 2P-24P Horizontal (180D wire inlet)-----Without cover					
PART NO.	VJxx01x2xxxxG			DWG NO.	8VJ0003	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		Aaron 2010.11.09	Aaron 2009.09.09			X. ±0.50
						X.X ±0.30
						X.XX ±0.10
						X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VJ02015200J0G</u>	<u>VJ08015200J0G</u>	<u>VJ0201520000G</u>	<u>VJ0801520000G</u>	<u>VJ0301520000G</u>	<u>VJ0401520000G</u>
<u>VJ0501520000G</u>	<u>VJ0601520000G</u>	<u>VJ0701520000G</u>	<u>VJ0901520000G</u>	<u>VJ1001520000G</u>	<u>VJ1101520000G</u>
<u>VJ1201520000G</u>	<u>VJ1301520000G</u>	<u>VJ1401520000G</u>	<u>VJ1501520000G</u>	<u>VJ1601520000G</u>	<u>VJ1701520000G</u>
<u>VJ1801520000G</u>	<u>VJ1901520000G</u>	<u>VJ2001520000G</u>	<u>VJ2101520000G</u>	<u>VJ2201520000G</u>	<u>VJ2301520000G</u>
<u>VJ2401520000G</u>	<u>VJ0301820000G</u>	<u>VJ0301020000G</u>	<u>VJ0201820000G</u>		