







P.C.B. LAYOUT



Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim L	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00
Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
TOL	±0.15					±0.25						
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim L	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	120.0	
Dim B	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	
TOL	±0.35					±0.40						


SIGN	DATE	DESCRIPTION	APPROVER
△	11.01'05	Standard spec is changed.	Marivn
△	01.18'07	Soldering temperature changed from 245° to 250°	Tason
△	01.18'07	Part NO is Changed	Tason
△	12.18'07	Screw is changed from M2.5 to M3.0	Marivn
△	08/26'09	Operating temperature changed from +105°C to +115°C	Aaron
△	08/26'09	And cULcs & VDE	Aaron
△	10/15'10	view revision	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing: Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass ,Ni plated
- Item 3 Wire guard solder pin: Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

△ Electrical UL / VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 10A/10A
- Wire range: 0.5-1.5mm²
- Solid wire(AWG): 16-26
- Stranded wire(AWG): 16-26
- Torque: 3.5Lb-In/0.4N.m
- Screw: M3.0
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:



△ TO xx 01 x 2 xxxx G

No. of poles end stackable design	0 Black (RAL9005)	0000:"@ "Logo (Standard)
	2 Red (RAL3001/D)	000A:"ANYTEK"Logo
02 2 CONTACTS	3 Orange(RAL2011/P)	Any special item by
03 3 CONTACTS	4 Yellow(RAL1018/A)	customer request,
...	5 Green(RAL6018/T)	please contact sales
24 24 CONTACTS	6 Blue (RAL5015/A)	department.
	8 Grey(RAL7035/D)	

RoHS
Pb<40,000ppm

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TO 5.0mm Series (2P-24P)						
PART NO.		TOxx01x2xxxxG			DWG NO.	8T00001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Aaron 2009.08.26	Aaron 2009.08.26		UNIT: mm		X.	±0.50
					SCALE: NONE		X.X	±0.30
							X.XX	±0.10
				SHEET: 01/01	REV: G		X"	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>TO0201520000G</u>	<u>TO0301520000G</u>	<u>TO0401520000G</u>	<u>TO0501520000G</u>	<u>TO0601520000G</u>	<u>TO0701520000G</u>
<u>TO0801520000G</u>	<u>TO0901520000G</u>	<u>TO1001520000G</u>	<u>TO1101520000G</u>	<u>TO1201520000G</u>	<u>TO1301520000G</u>
<u>TO1401520000G</u>	<u>TO1501520000G</u>	<u>TO1601520000G</u>	<u>TO1701520000G</u>	<u>TO1801520000G</u>	<u>TO1901520000G</u>
<u>TO2001520000G</u>	<u>TO2101520000G</u>	<u>TO2201520000G</u>	<u>TO2301520000G</u>	<u>TO2401520000G</u>	<u>TO0201820000G</u>
<u>TO0501820000G</u>	<u>TO0301820000G</u>				