



#### ELECTRICAL CHARACTERISTICS

- Impedance: 50 Ohm
- Working frequency: 1GHz max
- Dielectric with standing voltage: 600V
- Insulation resistance 5000: 14 OHMS
- Contact resistance < 5 m Ohm
- Insertion lost: < 0.2 dB

#### MECHANICAL CHARACTERISTICS

- Mating force per set of contact 0.4 N to 9 N
- Mating endurance 500
- Temperature -55°C to +125 °C

#### TOOLING

- Coaxial contact extraction tool 8630-07A

DM537405001NCLF	STRAIGHT MALE COAXIAL CONTACT	1.70	2.46	3.13	3.84	RG 188 A/U RG 179 B/U RG 316 /U
PART NUMBER	DESIGNATION	$\phi A^{+0.10}_0$	$\phi B^{\pm 0.05}$	$\phi C^{+0.10}_0$	$\phi D^{\pm 0.10}$	CABLE REF.

#### NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

rev	ecn no	dr	date
A	LS05-0086	MPE	2005/10/14
B	LS05-0107	MPE	2005/12/20
C	LS07-0001	LGO	2007/01/09
D	F10-0086	LSA	2010/08/20
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS		OTHERWISE SPECIFIED					
Dr	PESSON	2005/10/14	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 5		
Eng	PESSON	2005/10/14			0.XX	±0.1				
Chr	LEGARE	2005/10/14	0.XX ±2		0.XXX	±0.1	ECN		F10-0086	
Appr	LEGARE	2005/10/14	Product family			D-SUB		Spec ref -		
			title STRAIGHT MALE COAXIAL CONTACT SOLDER TO CABLE			dwg no C01-8639-2155			Rev. D	
catalog no						CUSTOMER			sheet 1 of 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DM537405001NCLF](#)