






Copyright FCI.

D


C

B

A



SECTION A-A



SECTION B-B

NOTES:


- 1-Material:phosphor bronze,thickness 0.20
- 2-Finish on contact area:see table
finish on termination:bright tin over nickel
- 3-Wire range:24-28 AWG
- 4-Max outer dia of wire insulator:1.02 mm
- 5-Current carrying capacity per contact:
 - 3.Amps max when crimped to #24 AWG
 - 2 Amps max when crimped to #26 AWG
 - 1 Amps max when crimped to #28 AWG
- 6-After 5 insertions into connector, contact retention must be 5 pounds axial load min
- 7-When contact is crimped to 24 AWG,the insulation support crimped height must be 1.78 mm max to ensure a proper insertion into housing
- 6-Packaging:Box of 500 contacts

NOTE : ROHS INFORMATIONS

The LF products meet European union directives and other country regulations as described in GS-22-008
Terminations plating spec : 2um Nickel min + 2um Sn min
Packaging Spec : see GS-14-920

PART NUMBER	Plating
8656451067LF	0.4μ Au / GXT
8656451067	0.4μ Au / GXT

rev	ecn no	dr	date
C	LS06-196	MPE	27/11/2006
D	LS08-0127	MPE	13/05/2008
E	LS08-0216	MPE	26/11/2008
F	I09-0128	AMR	2009-07-07
G	I09-0152	AMR	2009-07-29
H	I10-0070	AMR	2010-03-09
J	111-0003	AMR	2011-01-06

www.fciconnect.com			surface - 		tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	C JARRY	1997-01-28	ANGULAR		LINEAR		0.X	±0.3	size A3	Scale 10:1
Eng	ABHILASH M R	2009-07-07					0.XX	±0.1		
Chr	ABHILASH M R	2009-07-07					0°	±2°		
Appr	SUDHIR VARMA	2009-07-07	Product family					-	Spec ref	
		title	CRIMP SOCKET					dwg no C01-8656-0418		Rev. J
			#Wire 24-28 Ø1.02 max							
			catalog no					-	CUSTOMER	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8656451067LF](#)