



DIMENSIONS      mm (inches)




METHOD OF INSERTION  
ON THE PCB = FLAT ROCK



# PCB DRILLING

component side






PART NUMBER		8609		<input type="checkbox"/>	<input type="checkbox"/>	81	<input type="checkbox"/>	7	<input type="checkbox"/>	5	<input type="checkbox"/>
PIN OUT				3	96						
rows a-b-c		_____		4	64						
rows a-c		_____									
NUMBER OF CONTACTS											
TERMINATION											
L = 13.10 ±0.20(.515)		_____		rear plug up		_____		96			
L = 17.10 ±0.20(.673)		_____		rear plug up + 1 wrap		_____		97			
PERFORMANCE CLASS											
DIN 41612 class 3		_____		_____		_____		_____		4	
DIN 41612 class 2		_____		_____		_____		_____		5	
DIN 41612 class 1		_____		_____		_____		_____		6	
TERMINATION TYPE											
TIN LEAD		_____		_____		_____		_____		000A	
LEAD FREE		_____		_____		_____		_____		ALF	

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000C

## European Views

www.fciconnect.com			surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 	mm 
TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	ROUILLARD	1993/06/16	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1.5	
Eng	TARON	1993/06/16			0.XX	±0.1			
Chr	LEGARE	1993/06/16			0.XXX	±0.1			
Appr	LEGARE	1993/06/16	0.xx	±2°			ECN	LS06-0095	
			Product family				DIN 8609	Spec ref -	
			title STRAIGHT FEMALE - STYLE C PRESS FIT REAR PLUG UP			dwg no C-8609-0366		Rev. 6	
catalog no			-			CUSTOMER		sheet 1 of 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86093968197765ALF](#)