


## DIMENSIONS



## TIN LEAD PART NUMBER

PART NUMBER


86093487313H55801E1

## LEAD FREE PART NUMBER


PART NUMBER

86093487313H55BWLF

## TERMINATION



PCB DRILLING  
component side






SPECIFICATION 801 = Grounding pins in position : a9-a11-a12-a13-b1-b2-b4  
or SPECIFICATION BW = Signal pins : other cavity b13-c1-c2-c3-c13

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

rev	ecn no	dr	date
A	-	-	1999/07/21
B	LS05-001	JTA	2005/03/01
C	LS06-0095	LGO	2006/06/21
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	TARON	1999/07/28	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1.5			
Eng	TARON	1999/07/28			0.XX	±0.1		ECN	LS06-0095		
Chr	LEGARE	1999/07/28			0.XX' ±2'	0.XXX					±0.1
Appr	LEGARE	1999/07/28	Product family				DIN 8609	Spec ref -			
			title STANDARD MALE 3 ROW C/2 48 CONTACTS				dwg no C-8609-0769			Rev. C	
catalog no			-				CUSTOMER			sheet	of 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86093487313H55BWLF](#)