











Copyright FCI.



SCALE 5:1



rev	ecn no	dr	date
A	S40287	BSL	1994-11-22
B	S05-0057	KBM	2005-02-25
C	S10-0205	NBR	2010-01-18
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface - 		tolerance std ISO 1302 ISO 406 ISO 1101						
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	BS LOW	1994-11-18	ANGULAR		LINEAR	0.X	±-	size A3	Scale 10:1		
Eng	BS LOW	1994-11-18				0.XX	±0.25				
Chr	KH LEE	2010-01-18	0°	±3°		0.XXX	±-	ECN	S10-0205		
Appr	JOEY NG	2010-01-18	Product family					-	Spec ref		-
		title MINITEK II R/A HEADER				dwg no 94277				Rev. C	
		catalog no				-		CUSTOMER		sheet 1 of 2	

CONFIDENTIAL

PRODUCT NO	POS	DIM X	DIM Y
94277-X04	2 X 2	2	4
X06	2 X 3	4	6
X08	2 X 4	6	8
X10	2 X 5	8	10
X12	2 X 6	10	12
X14	2 X 7	12	14
X16	2 X 8	14	16
X18	2 X 9	16	18
X20	2 X 10	18	20
X22	2 X 11	20	22
X24	2 X 12	22	24
X26	2 X 13	24	26
X28	2 X 14	26	28
X30	2 X 15	28	30
X32	2 X 16	30	32
X34	2 X 17	32	34
X36	2 X 18	34	36
X38	2 X 19	36	38
X40	2 X 20	38	40
X42	2 X 21	40	42
X44	2 X 22	42	44
X46	2 X 23	44	46
X48	2 X 24	46	48
X50	2 X 25	48	50

PRODUCT DESCRIPTION CODE :

XXXXX-XXXLF

LEAD FREE (SEE NOTE 4)

EXTENSION NUMBER

TERMINAL PLATING

BASE NUMBER

NOTES:

1. MATERIAL:

BODY : HIGH TEMPERATURE PLASTIC UL 94V-0 BLACK

PIN : COPPER ALLOY

2. TOLERANCE UNLESS OTHERWISE NOTED ± 0.25

③ STAND-OFF DESIGN FOR 2X2 POS. REFERS TO FIG. 1.

④ P/N:94277-XXXLF IS SAME AS P/N:94277-XXX. THE SUFFIX 'LF' IS ADDED JUST FOR EASY LEAD FREE IDENTIFICATION

5. THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

6. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57MM MINIMUM THICK CIRCUIT BOARD.

7. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

△ 8. A △C SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.





FIG. 1

SEE NOTE 3



RECOMMENDED HOLE LAYOUT
SCALE 5:1

CONFIDENTIAL

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection MM
			TOLERANCES UNLESS OTHERWISE SPECIFIED		
Dr	BS LOW	1994-11-18	ANGULAR 0° ±3°	0.X ±-	size A3
Eng	BS LOW	1994-11-18		0.XX ±0.25	Scale 10:1
Chr	KH LEE	2010-01-18		0.XXX ±-	ECN S10-0205
Appr	JOEY NG	2010-01-18	Product family		Spec ref
FCI			MINITEK II R/A HEADER		Rev. C
-			catalog no	dwg no 94277	sheet 2 of 2
			CUSTOMER		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[94277-104LF](#)