



DIMENSIONS



PCB LAYOUT




CONTACT ARRANGEMENT

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
a	✓	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✓
b	✓	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✗	✓
✗ STANDARD CONTACT      ✓ FMLB CONTACT      □ EMPTY CAVITY																

GENERAL CHARACTERISTICS & RoHS INFO  
REFER DRAWING C-8609-0000A

TERMINATION



ORDERING INFORMATION

SERIES	8609	2	32	5	3	13	7	4	5	UNLF
ROWS FITTED WITH CONTACTS										
ROW a b	2									
NO. OF CONTACTS	32									
TYPE OF INSULATOR	2 ROW MALE INSULATOR									
METHOD OF MOUNTING	STANDARD MOUNTING - STYLE B/2									
TERMINATION	ANGLED SPILL									
OPTIONS	NO OPTION									
PERFORMANCE CLASS	DIN 41612 CLASS 3									
PITCH PER ROW	2.54 mm									
LEAD FREE VERSION	UNLF									

mat'l. code	surface	tolerance	projection	product family
SEE DWG C-8609-0000A	ISO 1302 ✓	ISO 406 ISO 1101	mm	8609
ltr	ecn no	dr	date	title
A	110-0074	KR	2010-03-20	DIN STANDARD HEADER
				ANGLED SPILL DIN 41612 STYLE B/2
				dwg no
				sheet 1 of 1
				size
				A3
				type Product Customer Drawing
sheet index	revision sheet	A	1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)  
[86092325313765UNLF](#)