


NOTES:

- 1) LABEL REQUIREMENT:
LABELS ARE M23053/5, WHITE. ACCEPTABLE SUBSTITUTION IS DAT-38-292 OR TRANSVINYL (DAT-63-292-2.5).
LOCATE APPROXIMATELY AS SHOWN.
- 2) TERMINUS ENDFACE REQUIREMENTS SHALL MEET GR-326 AND IEC 61300-3-35.
- 3) MAX IL @ 1310 nm SHALL BE 0.5 dB PER CONNECTION.

REVISION HISTORY - ALL SHEETS ARE AT THE SAME REVISION

REV	DESCRIPTION	DATE	APPROVED
-	INITIAL RELEASE	2017/11/13	



ITEM NO.	PART NO.	DESCRIPTION	QTY/LENGTH
7	AFSI-PRE T BOX	BOX, SMALL FIBER CABLE 10X10X2 W/AFSI GRAPHICS	1
6	WTRO-0200	CABLE, 2 FIBER 9/125 TACTICAL BREAKOUT	3.25 FEET
5	BLCC1588709-1	CONNECTOR KIT, LC, SIMPLEX, SM JUMPER, 1.6-2.0MM	2
4	202K121-25-0	SHRINK BOOT, RAYCHEM	1
3	M85049/69-11W	BACKSHELL SHRINK BOOT ADAPTER	1
2	M801-SU2N	ARINC 801 TERMINI, UPC, NON-PULL PROOF	2
1	FS801-11P02ACN	PLUG ASSEMBLY, ARINC, SH 11	1

P1	PINOUT DIAGRAM	B LABEL INFORMATION
A		A
B		B

MATERIAL:		DFTR/Designer: 2017/10/20	Amphenol FSI
		Check By: B. Waite 2017/10/24	
		Manufacturing: B. Waite 2017/10/24	
		Market Manager/PLM: Q. Abraham 2017/10/25	
DRILLED HOLE DIAMETER TOLERANCE		Configuration Management: L. Brown 2017/11/13	TITLE: 2 CHANNEL ARINC PLUG TO LC ASSEMBLY, SM
DO NOT SCALE DRAWING UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL ON ANGLES ±3° 1 PL ±.1 2 PL ±.02 3 PL ±.010 INTERPRET DIM AND TOL PER ASME 14.5M-1994		This Document contains proprietary information and such information is prohibited from disclosure to others, publication or duplication in whole or in part without written permission from Amphenol Fiber Systems International. Copyright © 2017 Amphenol Fiber Systems International. Non published work. All rights reserved.	
NEXT ASSY	USED ON	SIZE: A	CAGE CODE: 0YPM2
APPLICATION		DWG NO: 16032202MD-D2	REV: -
		SCALE: NONE	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[16032202MD-D2](#)