

PRODUCT NUMBER


71600-YXXLF

LEAD FREE, SEE NOTE 6

TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2

OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5



NOTES:

- 1 - PLASTIC MAT'L : GLASS FILLED HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: GREY
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PRODUCT PACKAGED IN TUBES.
- 4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- 5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.
- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO LEFT AND RIGHT POLARIZING SLOT.
- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT POLARIZING SLOT.
- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT
- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT
- 6 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.

COVER ORIENTATION

CABLE ENTRY

TRIANGLE SIDE

D D SECTION

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family 2.54MM IDC
lfr	ecn no	dr	date	tolerances unless otherwise specified		mm	title
AP	F12-0046	LMU	12.04.25	angles	X.X ±0.3		QUICKIE III FEM
				linear	X.XX ±0.13		0.76µm Au
AJ	F05-0171	LMU	05.04.07		X.XXX ±0.05	scale 5:1	
AK	F05-0180	LMU	05.04.22	dr	D.LE	01.01.24	dwg no
AL	F06-0270	LMU	06.09.12	engr	P.NZ	01.01.24	sheet 1 of 2
AM	F06-0274	LMU	06.09.25	chr	JF.N	01.01.24	size
AN	F09-0233	LMU	09.12.15	appd	P.NZ	01.01.24	A3
sheet index	revision sheet	AP	AE				type
		1	2				CUSTOMER Drawing

PDM: Rev:AP

STATUS Released

Printed: Apr 27, 2012

CORE RANGE

STRAIN RELIEF	Nbr OF POSITIONS
0/1	04
0/1	06
0/1	08
0/1	10
0/1	14
0/1	16
0/1	18
0/1	20
0/1	24
0/1	26
0/1	30
0/1	34
0/1	40
0/1	50
0/1	60
0/1	64

PLATING

0.76µm GOLD ON CONTACT AREA
1.27 µm Ni REMAINDER OF PRODUCT

CATALOGUE RANGE

STRAIN RELIEF	Nbr OF POSITIONS
2/6	04
2/6	06
2/6	08
2/6	10
2/6	14
2/6	16
2/6	18
2/6	20
2/6	24
2/6	26
2/6	30
2/6	34
2/6	40
2/6	50
2/6	60
2/6	64

PLATING


0.76µm GOLD ON CONTACT AREA
1.27 µm Ni REMAINDER OF PRODUCT

624


304

204 / 224


004

DASHES NOT
AVAILABLE


WITHOUT STRAIN RELIEF






WITH LOW PROFILE STRAIN RELIEF






WITH STANDARD STRAIN RELIEF



WITH LATCHING STRAIN RELIEF

LOW PROFILE
STRAIN RELIEFSTANDARD
STRAIN RELIEFLATCHING STRAIN RELIEF
FOR SLIM HEADER

71600-6YYLF	●					●
71600-3YYLF		●	●			
71600-2YYLF	●				●	
71600-1YYLF	●			●		
71600-0YYLF	●		●			
PRODUCT NUMBER	WITH	WITHOUT	STANDARD	WITHOUT	LOW PROFILE	LATCHING
	CENTRAL KEY		STRAIN RELIEF			

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE				
ltr	ecn no	dr	date	tolerances unless otherwise specified						title IDC RECEPT DR				
X	F70666	AAN	97.11.05	angles	linear									
Y	F10121	DLE	01.01.24											
AA	F10199	GCO	01.04.26					scale N/A						
AB	F03019	DLE	03.01.23	dr	D.LE	01.01.24				dwg no		sheet 2 of -		size
AC	F05-0180	LMU	05.04.22	enrg	P.NZ	01.01.24				71600				A3
AD	F06-0270	LMU	06.09.12	chr	JF.N	01.01.24								
AE	F06-0274	LMU	06.09.25	appd	P.NZ	01.01.24								
sheet index		revision sheet												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[71600-144LF](#) [71600-644LF](#) [71600-344LF](#)