

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

3D model search

Customer drawing search

Free search

Search by category

E-Services

Distributor list

Start > Search=61729-1011RLF* > 61729-1011RLF

61729-1011RLF

61729-1011RLF -
USB : Type B,
Receptacle, Through
Hole, 30u GXT
Contact, 4 Pins, Full
Back Shield with
Bright Tin Plating,
1.57 mm PCB, Black
HSG, Tape and Reel
packing

ACTIVE

RoHS
Compliant

Distributor Stock

[Add to Favorites](#)[Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)[Sample request](#)[Price request](#)Customer
drawingEnvironmental
Compliance Report

Specifications

Download document

Approvals / Certifications Dimensional General Mounting Physical Other Features

Approvals / Certifications

USB 2.0 Qualified	Yes
USB 3.0 Qualified	No

Dimensional

Thickness (Board - recommended)	1.57 mm
Thickness (Panel - max)	2.67 mm

General

Hold Down Style	Standard
Number of contacts	4
Orientation	Right Angle
Pin Orientation	Standard
Product Type	Receptacle
Shell Options	Back Shield
Style	B Type
Sensor Contact Options	without Sensor Contact
Series Number	61729
Single or Dual Stack	Single

Mounting

Mounting flange / Hole options	None
Mounting style	Through Hole

Physical

Color (Housing)	Black
Material (Housing)	Glass - Fiber Filled Thermoplastic, UL 94V-0
Plating (Contact area)	30u" GXT
Plating (Shell)	Pure Tin / Nickel Under Plating
Plating (Tail)	100u" Pure Tin

Other Features

Most Popular Configuration	Not Applicable
Packaging (Options)	Tape and Reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[61729-1011RLF](#)