




Ansicht ohne O-Ring
View without O-Ring




A-A
Einschraubloch/
FEMALE COUNTER-PART
5:1



Komponenten Liste/ Component List		
Stk	Benennung Discription	Material
1	Druckstutzen Fitting	A6061-T6 / AlMg1SiCu (EN AW 6061-T6)
1	O-Ring (Druckstutzen/ Fitting)	Ethylen acrylic rubber (Vamac LT) black Hardness: 70 ± 5 (Shore A)
1	Adapter	1.4305 (JIS SUS303)
1	Messzelle Measuring Cell	1.4542 (JIS SUS630)
1	O-Ring (Stecker/ Connector)	Silicon VMQ 70 Hardness: 70 ± 5 (Shore A)
1	Leiterplatte PCB	Epoxy-glass
1	Stecker Connector	PBT-GF 30 schwarz / black



Verwendungsbereich Application				Tolerierung/ Tolerances		Maßstab Scale		Gewicht Weight	
803252 Freigegeben		Maße/ Dim. mm		ISO 14405 - (E) DIN ISO 2768-mK		2:1		0.016 kg	
						Werkstoff/ Material			
						Benennung/ Naming			
				Name		16.12.20 Frost			
				Gepr.		16.12.20 Zühlke			
				Check					
									
REV		Änderung/ Change		Dat		Name		Zeichnung_ Nr./ Drawing Number: Iteration	
								Blatt/Sheet	
								1	
								Size: A2	
								1 Bl./Sh.	
								Mord: 1_150054818D	
								Frs. f.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[803252](#)