


REV.	DATE	DESCRIPTION
B	04/31/03	UPDATE DRAWING FORMAT



REMARK:
ROCKWELL HARDNESS OF
55 MAX. ON 15-T SCALE
(HEAT TREAT FOR 30 MIN.
AT 900°F BEFORE PLATING)

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN () ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex							
8						DRAWN	G.R.S.		04/31/03						
7															
6															
5															
4					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED		PART DESCRIPTION FERRULE-SMA-316DNKL							
3						ISSUED									
2															
1	FERRULE	COPPER	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	SHEET	1 OF 1		PART NO. FRL-SMA-316DNKL						
	DESCRIPTION	MATERIAL	FINISH	QTY		DO NOT SCALE DRAWING									
						CAD FILE	C:/MISC/FRL-SMA-316DNKL.DWG	DWG. NO.	FRL-SMA-316DNKL.DWG	REV.	B	SIZE	A	SCALE	NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[FRL-SMA-316DNKL](#)