


MIL-DTL-83723/59-1 PLUG DUST CAP

MIL-DTL-26500 Series III

M83723/59-1	Shell Size	Finish	Style
Designated Receptacle Cover	8 10 12 14 16 18 20 22 24	W - Cadmium R - Electroless Nickel A - Anodized Black Z - Black Zinc Nickel	P - w/ Chain Length 8in + .25in C - w/ Chain Length 5in + .25in R - w/ Rope Length 5in + .25in T - w/ Rope Length 8in + .25in N - w/o Chain




Shell Size	A Thread UNEF-2A		C Ø Max.		G Ø Max.		Chain S/Assembly L		SS Rope S/Assembly L	
							+6.35 -0.0		+6.35 -0.0	
	mm	in	mm	in	mm	in	mm	in	mm	in
8	0.5625-24	0.02-0.94	19.71	0.78	14.25	0.56	127.0	5	203.20	8
10	0.6875-24	0.03-0.94	23.01	0.91	17.68	0.70				
12	0.8750-20	0.03-0.79	27.38	1.078	22.23	0.88				
14	0.9375-20	0.04-0.79	28.98	1.14	23.75	0.94				
16	1.0625-18	0.04-0.71	32.16	1.27	26.97	1.06				
18	1.1875-18	0.050.71	34.93	1.378	30.15	1.19				
20	1.3125-18	0.050.71	38.35	1.51	33.32	1.31				
22	1.4375-18	0.050.71	41.28	1.63	36.50	1.44				
24	1.5625-18	0.060.71	44.70	1.76	39.67	1.56				

M83723/59-2 BAYONET PLUG DUST CAP

MIL-DTL-26500 Series III

M83723/59-2	Shell Size	Finish	Style
Designated Receptacle Cover	8 10 12 14 16 18 20 22 24	W - Cadmium R - Electroless Nickel A - Anodized Black Z - Black Zinc Nickel	P - w/ Chain Length 8in + .25in C - w/ Chain Length 5in + .25in R - w/ Rope Length 5in + .25in T - w/ Rope Length 8in + .25in N - w/o Chain




Shell Size	H Max		Ø J		Ø K		Ø N		Ø NN		Chain S/Assembly L		SS Rope S/Assembly L	
			+0.0 - 0.13		+0.13 - 0.0		+0.0 - 0.10		+0.0 - 0.08		+6.35 -0.0		+6.35 -0.0	
	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in
8	19.46	0.76	13.61	0.534	12.07	0.48	2.57	0.10	1.98	0.08	127.0	5	203.20	8
10	23.01	0.91	16,74	0.656	14.63	0.58	2.39	0.04	2.36	0.09				
12	27.38	1.08	21.06	0.83	18.95	0.75								
14	28.98	1.14	22.81	0.90	20.70	0.81								
16	32.16	1.27	26.04	1.03	23.93	0.94								
18	34.93	1.38	28.73	1.13	26.62	1.05								
20	38.35	1.51	31.90	1.26	29.74	1.17								
22	41.28	1.62	35.08	1.38	32.94	1.30								
24	44.70	1.76	38.25	1.51	36.07	1.42								

MIL-DTL-83723/60-1 RECEPTACLE DUST CAP

MIL-DTL-26500 Series III

M83723/60-1	Shell Size	Finish	Style
Designated Receptacle Cover	8 10 12 14 16 18 20 22 24	W - Cadmium R - Electroless Nickel A - Anodized Black Z - Black Zinc Nickel	P - w/ Chain Length 8in + .25in C - w/ Chain Length 5in + .25in R - w/ Rope Length 5in + .25in T - w/ Rope Length 8in + .25in N - w/o Chain




All dimensions are in mm.

Shell Size	A Thread UNEF-2A		C Ø Max.		Chain S/Assembly L		SS Rope S/Assembly L	
	mm	in	mm	in	+6.35 -0.0		+6.35 -0.0	
8	0.5625-24	0.02-0.94	19.71	0.78	127.0	5	203.20	8
10	0.6875-24	0.03-0.94	23.01	0.91				
12	0.8750-20	0.03-0.79	27.38	1.078				
14	0.9375-20	0.04-0.79	28.98	1.14				
16	1.0625-18	0.04-0.71	32.16	1.27				
18	1.1875-18	0.050.71	34.93	1.378				
20	1.3125-18	0.050.71	38.35	1.51				
22	1.4375-18	0.050.71	41.28	1.63				
24	1.5625-18	0.060.71	44.70	1.76				

MIL-DTL-83723/60-2 BAYONET RECEPTACLE DUST CAP

MIL-DTL-26500 Series III

M83723/60-2	Shell Size	Finish	Style
Designated Receptacle Cover	8	W - Cadmium R - Electroless Nickel A - Anodized Black Z - Black Zinc Nickel	P - w/ Chain Length 8in + .25in C - w/ Chain Length 5in + .25in R - w/ Rope Length 5in + .25in T - w/ Rope Length 8in + .25in N - w/o Chain
	10		
	12		
	14		
	16		
	18		
	20		
	22		
24			



Shell Size	A MAX		Ø B MAX		Ø C MAX		H MIN		Chain S/Assembly L Max		SS Rope S/Assembly L	
					+0.13 - 0.0				+6.35 -0.0		+6.35 -0.0	
	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in
8	19.71	0.78	16.20	0.64	13.72	0.54	2.01	0.08	127.0	5	203.20	8
10	23.01	0.91	19.40	0.76	16.81	0.66	2.39	0.09				
12	27.38	1.08	23.80	0.94	21.13	0.83						
14	28.98	1.14	25.50	1.00	22.89	0.90						
16	32.16	1.27	28.70	1.123	26.11	1.027						
18	34.93	1.38	31.50	1.24	28.80	1.13						
20	38.35	1.51	34.60	1.36	32.03	1.26						
22	41.28	1.63	37.80	1.49	35.15	1.38						
24	44.70	1.76	40.90	1.61	38.38	1.51						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[M8372359108AC](#) [M8372359108AN](#) [M8372359108AP](#) [M8372359108AR](#) [M8372359108AT](#) [M8372359108RC](#)
[M8372359108RN](#) [M8372359108RP](#) [M8372359108RR](#) [M8372359108RT](#) [M8372359108WC](#) [M8372359108WN](#)
[M8372359108WP](#) [M8372359108WR](#) [M8372359108WT](#) [M8372359108ZC](#) [M8372359108ZN](#) [M8372359108ZP](#)
[M8372359108ZR](#) [M8372359108ZT](#) [M8372359110AC](#) [M8372359110AN](#) [M8372359110AP](#) [M8372359110AR](#)
[M8372359110AT](#) [M8372359110RN](#) [M8372359110RP](#) [M8372359110RR](#) [M8372359110RT](#) [M8372359110WC](#)
[M8372359110WN](#) [M8372359110WP](#) [M8372359110WR](#) [M8372359110WT](#) [M8372359110ZC](#) [M8372359110ZN](#)
[M8372359110ZP](#) [M8372359110ZR](#) [M8372359110ZT](#) [M8372359112AC](#) [M8372359112AN](#) [M8372359112AP](#)
[M8372359112AR](#) [M8372359112AT](#) [M8372359112RN](#) [M8372359112RP](#) [M8372359112RR](#) [M8372359112RT](#)
[M8372359112WC](#) [M8372359112WN](#) [M8372359112WP](#) [M8372359112WR](#) [M8372359112WT](#) [M8372359112ZC](#)
[M8372359112ZN](#) [M8372359112ZP](#) [M8372359112ZR](#) [M8372359112ZT](#) [M8372359114AC](#) [M8372359114AN](#)
[M8372359114AP](#) [M8372359114AR](#) [M8372359114AT](#) [M8372359114RC](#) [M8372359114RN](#) [M8372359114RP](#)
[M8372359114RR](#) [M8372359114RT](#) [M8372359114WC](#) [M8372359114WN](#) [M8372359114WP](#) [M8372359114WR](#)
[M8372359114WT](#) [M8372359114ZC](#) [M8372359114ZN](#) [M8372359114ZP](#) [M8372359114ZR](#) [M8372359114ZT](#)
[M8372359116AC](#) [M8372359116AN](#) [M8372359116AP](#) [M8372359116AR](#) [M8372359116AT](#) [M8372359116RC](#)
[M8372359116RN](#) [M8372359116RP](#) [M8372359116RR](#) [M8372359116RT](#) [M8372359116WC](#) [M8372359116WN](#)
[M8372359116WP](#) [M8372359116WR](#) [M8372359116WT](#) [M8372359116ZC](#) [M8372359116ZN](#) [M8372359116ZP](#)
[M8372359116ZR](#) [M8372359116ZT](#) [M8372359118AC](#) [M8372359118AN](#)