

1






2

3

4

PART NO.

20021121



NOTES:

1.MATERIAL:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94-V0 BLACK.
TERMINAL: COPPER ALLOY

2.THE HOUSING WILL WITHSTAND EXPOSURE TO 260-C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION INFRA-RED
OR VAPOR PHASE REFLOW OVEN.

3.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

4.PRODUCT SPEC: GS-12-629

5.PACKAGE SPEC: GS-14-1420

spec ref				dr	ZK HU	2012-8-1	projection 	MM 	size	A3	scale	10.000		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	ZK HU	2012-8-1			ecn no	ELX-N-14370				
ISO 1101 ISO 406				chr	RICK BIAN	2012-8-1								
				appr	RICK BIAN	2012-8-1	product family			rel level RELEASED				
surface ISO 1101 	linear	0.X	± 0.30		title	MINITEK 127 UBShrouded HDR VT SMT				dwg no	20021121		rev	J
		0.XX	± 0.20											
		0.XXX	± 0.10											
		angular	2~	± 2°	www.fci.com		cat. no.		Product - Customer Drw			sheet 1 of 2		

1

2

3

PDS: Rev :J

STATUS:Released

Printed: Mar 29, 2013

1


2

3

4

PART NO.	POS.	DIM*X'	DIM*Y'	DIM*Z'
20021121-X0X06XXLF	2 X 3	3.81	2.54	1.27
20021121-X0X08XXLF	2 X 4	5.08	3.81	2.54
20021121-X0X10XXLF	2 X 5	6.35	5.08	3.81
20021121-X0X12XXLF	2 X 6	7.62	6.35	5.08
20021121-X0X14XXLF	2 X 7	8.89	7.62	6.35
20021121-X0X16XXLF	2 X 8	10.16	8.89	7.62
20021121-X0X18XXLF	2 X 9	11.43	10.16	8.89
20021121-X0X20XXLF	2 X 10	12.70	11.43	10.16
20021121-X0X22XXLF	2 X 11	13.97	12.70	11.43
20021121-X0X24XXLF	2 X 12	15.24	13.97	12.70
20021121-X0X26XXLF	2 X 13	16.51	15.24	13.97
20021121-X0X28XXLF	2 X 14	17.78	16.51	15.24
20021121-X0X30XXLF	2 X 15	19.05	17.78	16.51
20021121-X0X32XXLF	2 X 16	20.32	19.05	17.78
20021121-X0X34XXLF	2 X 17	21.59	20.32	19.05
20021121-X0X36XXLF	2 X 18	22.86	21.59	20.32
20021121-X0X38XXLF	2 X 19	24.13	22.86	21.59
20021121-X0X40XXLF	2 X 20	25.40	24.13	22.86
20021121-X0X42XXLF	2 X 21	26.67	25.40	24.13
20021121-X0X44XXLF	2 X 22	27.94	26.67	25.40
20021121-X0X46XXLF	2 X 23	29.21	27.94	26.67
20021121-X0X48XXLF	2 X 24	30.48	29.21	27.94
20021121-X0X50XXLF	2 X 25	31.75	30.48	29.21
20021121-X0X52XXLF	2 X 26	33.02	31.75	30.48
20021121-X0X54XXLF	2 X 27	34.29	33.02	31.75
20021121-X0X56XXLF	2 X 28	35.56	34.29	33.02
20021121-X0X58XXLF	2 X 29	36.83	35.56	34.29
20021121-X0X60XXLF	2 X 30	38.10	36.83	35.56
20021121-X0X62XXLF	2 X 31	39.37	38.10	36.83
20021121-X0X64XXLF	2 X 32	40.64	39.37	38.10
20021121-X0X66XXLF	2 X 33	41.91	40.64	39.37
20021121-X0X68XXLF	2 X 34	43.18	41.91	40.64
20021121-X0X70XXLF	2 X 35	44.45	43.18	41.91
20021121-X0X72XXLF	2 X 36	45.72	44.45	43.18
20021121-X0X74XXLF	2 X 37	46.99	45.72	44.45
20021121-X0X76XXLF	2 X 38	48.26	46.99	45.72
20021121-X0X78XXLF	2 X 39	49.53	48.26	46.99
20021121-X0X80XXLF	2 X 40	50.80	49.53	48.26
20021121-X0X82XXLF	2 X 41	52.07	50.80	49.53
20021121-X0X84XXLF	2 X 42	53.34	52.07	50.80
20021121-X0X86XXLF	2 X 43	54.61	53.34	52.07
20021121-X0X88XXLF	2 X 44	55.88	54.61	53.34
20021121-X0X90XXLF	2 X 45	57.15	55.88	54.61

PART NO.	POS.	DIM*X'	DIM*Y'	DIM*Z'
20021121-X0X92XXLF	2 X 46	58.42	57.15	55.88
20021121-X0X94XXLF	2 X 47	59.69	58.42	57.15
20021121-X0X96XXLF	2 X 48	60.96	59.69	58.42
20021121-X0X98XXLF	2 X 49	62.23	60.96	59.69
20021121-X0XA0XXLF	2 X 50	63.50	62.23	60.96



20021121-X X X XX X X LF

LEAD FREE

PLATING ON CONTACT AREA

1: GOLD FLASH AT CONTACT, 1.27um MIN. MATTE TIN AT TAIL

2: GOLD FLASH AT CONTACT, GOLD FLASH AT TAIL

4: 0.25um Au MIN. AT CONTACT, 1.27um MIN.MATTE TIN AT TAIL

5: 0.25um Au MIN. AT CONTACT, GOLD FLASH AT TAIL

6: 0.38um GXT MIN. AT CONTACT, 1.27um MIN.MATTE TIN AT TAIL

7: 0.38um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

8: 0.76um GXT MIN. AT CONTACT, 1.27um MIN.MATTE TIN AT TAIL

9: 0.76um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

PACKING STYLE

T: TUBE

D: TUBE + CAP

C: TAPE & REEL + CAP

PIN NO. SEE TABLE

MATING LENGTH(DIM*A')

0: 3.05MM

RESERVE CODE

0: STANDARD

POST OPTION

0: WITHOUT POST

1: WITH POST

spec ref	dr	ZK HU	2012-8-1	projection	MM	size	A3	scale	5.000
tolerance std	eng	ZK HU	2012-8-1			ecn no	ELX-N-14370		
ISO 1101	chr	RICK BIAN	2012-8-1			rel level	RELEASED		
ISO 406	appr	RICK BIAN	2012-8-1	product family					
surface	linear	0.X	±0.30	FCI	MINITEK 127 UBSHROUDED HDR	dwg no	20021121	rev	J
		0.XX	±0.20		VT SMT				
		0.XXX	±0.10						
ISO 1101	angular	0~	±2'	www.fci.com	cat. no.	Product - Customer Drw	sheet 2 of 2		

1

2

3

PDS: Rev :J

STATUS:Released

Printed: Mar 29, 2013

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

<u>20021121-00006T1LF</u>	<u>20021121-00008T1LF</u>	<u>20021121-00010T1LF</u>	<u>20021121-00012T1LF</u>	<u>20021121-00014T1LF</u>
<u>20021121-00016T1LF</u>	<u>20021121-00018T1LF</u>	<u>20021121-00020T1LF</u>	<u>20021121-00022T1LF</u>	<u>20021121-00024T1LF</u>
<u>20021121-00026T1LF</u>	<u>20021121-00028T1LF</u>	<u>20021121-00030T1LF</u>	<u>20021121-00032T1LF</u>	<u>20021121-00034T1LF</u>
<u>20021121-00036T1LF</u>	<u>20021121-00038T1LF</u>	<u>20021121-00040T1LF</u>	<u>20021121-00042T1LF</u>	<u>20021121-00044T1LF</u>
<u>20021121-00046T1LF</u>	<u>20021121-00048T1LF</u>	<u>20021121-00050T1LF</u>	<u>20021121-00052T1LF</u>	<u>20021121-00054T1LF</u>
<u>20021121-00056T1LF</u>	<u>20021121-00058T1LF</u>	<u>20021121-00060T1LF</u>	<u>20021121-00062T1LF</u>	<u>20021121-00064T1LF</u>
<u>20021121-00066T1LF</u>	<u>20021121-00068T1LF</u>	<u>20021121-00070T1LF</u>	<u>20021121-00072T1LF</u>	<u>20021121-00074T1LF</u>
<u>20021121-00076T1LF</u>	<u>20021121-00078T1LF</u>	<u>20021121-00080T1LF</u>	<u>20021121-00082T1LF</u>	<u>20021121-00084T1LF</u>
<u>20021121-00086T1LF</u>	<u>20021121-00088T1LF</u>	<u>20021121-00090T1LF</u>	<u>20021121-00092T1LF</u>	<u>20021121-00094T1LF</u>
<u>20021121-00096T1LF</u>	<u>20021121-00098T1LF</u>	<u>20021121-000A0T1LF</u>	<u>20021121-00006T4LF</u>	<u>20021121-00008T4LF</u>
<u>20021121-00010T4LF</u>	<u>20021121-00012T4LF</u>	<u>20021121-00014T4LF</u>	<u>20021121-00016T4LF</u>	<u>20021121-00018T4LF</u>
<u>20021121-00020T4LF</u>	<u>20021121-00022T4LF</u>	<u>20021121-00024T4LF</u>	<u>20021121-00026T4LF</u>	<u>20021121-00030T4LF</u>
<u>20021121-00032T4LF</u>	<u>20021121-00034T4LF</u>	<u>20021121-00036T4LF</u>	<u>20021121-00038T4LF</u>	<u>20021121-00040T4LF</u>
<u>20021121-00042T4LF</u>	<u>20021121-00044T4LF</u>	<u>20021121-00046T4LF</u>	<u>20021121-00048T4LF</u>	<u>20021121-00050T4LF</u>
<u>20021121-00052T4LF</u>	<u>20021121-00054T4LF</u>	<u>20021121-00056T4LF</u>	<u>20021121-00058T4LF</u>	<u>20021121-00060T4LF</u>
<u>20021121-00062T4LF</u>	<u>20021121-00064T4LF</u>	<u>20021121-00066T4LF</u>	<u>20021121-00068T4LF</u>	<u>20021121-00070T4LF</u>
<u>20021121-00072T4LF</u>	<u>20021121-00074T4LF</u>	<u>20021121-00076T4LF</u>	<u>20021121-00078T4LF</u>	<u>20021121-00080T4LF</u>
<u>20021121-00082T4LF</u>	<u>20021121-00084T4LF</u>	<u>20021121-00086T4LF</u>	<u>20021121-00088T4LF</u>	<u>20021121-00090T4LF</u>
<u>20021121-00092T4LF</u>	<u>20021121-00094T4LF</u>	<u>20021121-00096T4LF</u>	<u>20021121-00098T4LF</u>	<u>20021121-000A0T4LF</u>
<u>20021121-00004T8LF</u>	<u>20021121-00006T8LF</u>	<u>20021121-00008T8LF</u>	<u>20021121-00010T8LF</u>	<u>20021121-00012T8LF</u>