

PRODUCT NUMBER
10119333-YXX-XXLF

PLATING
1=0.76µm GXT/GOLD ON CONTACT
2µm TIN MIN ON TAILS
4=2µm TIN MIN FULL PLATED

RoHS COMPATIBLE
NOTE 4


TOTAL NUMBER OF
POSITIONS :
02 TO 25 POS

PACKAGING, NOTE 3


STYLE	DIM"A"±0.2
01	5.84
02	8.08
03	10.67
04	3.00

NOTES:




- 1 - MATERIAL:
 - BODY: HIGH TEMPERATURE THERMOPLASTIC
UL94V-0 COLOR BLACK
 - PIN : COPPER ALLOY
- 2 - TO DETERMINATE DIMENSIONS :
N = NUMBER OF POSITIONS
EXAMPLE : 8 POS x 2.54=20.32
- 3 - PACKAGING:
 - A = TAPE & REEL PACKAGING WITH PICK -UP CAP
AS PER GS-14-2357
 - K= T&R PACKAGING WITHOUT PICK UP CAP,
AS PER GS-14-2357
 - = POLYBAGS
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS :
 - a - PLATING :
"LF" MEANS THE PRODUCT IS LEAD FREE
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATED
 - b - MANUFACTURING PROCESS COMPATIBILITY :
THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN
 - c - LABELLING :
MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT : SEE GS-47-0004
- 5 - PRODUCT SPECIFICATIONS AS PER BUS-12-114
EXCEPT PIN RETENTION FORCE 5N MIN.



SCALE 3:1



PCB LAYOUT



spec ref	dr	Aymeric Soudy	2014/02/21	projection	MM	size	A3	scale	5:1
tolerance std	eng	Pro Engineer 1	2014/04/23	chr	Laurent Mulin	2014/04/23	ecn no	-	
ISO 406	appr	J M Maire	2014/04/23	product family	BSTIK	rel level	Released		
ISO 1101									
surface	linear	0.X	±0.3	FCI	2.54mm UNSH HEADER HORIZ	dwg no	10119333	rev	A
ISO 1302	angular	0°	±2°	www.fci.com	SINLE ROW SMT				
				cat. no.	-	Product - Customer Drw	sheet 1 of 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10119333-101A22LF](#) [10119333-101K04LF](#) [10119333-103A05LF](#) [10119333-402K03LF](#) [10119333-101A04LF](#)
[10119333-403A03LF](#) [10119333-103A11LF](#) [10119333-103A03LF](#) [10119333-101A03LF](#) [10119333-101A06LF](#)
[10119333-401A06LF](#)