



PRODUCT NUMBER
SEE SHEET 3




2.35 ϕ OF EVEN COLUMNS
2.25 ϕ OF ODD COLUMNS




SECTION AA-AA

spec ref	---	dr	Lin-Soe Ngwe	2013/02/19	projection	MM	size	A2	scale	6:1
tolerance std	ASME Y14.5M	eng	Jackie Chen	2015/02/03	chr	-	ecn no	ELX-DG-20160-1	rel level	Released
surface	✓	appr	Collins Lu	2015/02/06	product family	AirMax VSE	cat. no.	10124408	rev	D
TOLERANCES UNLESS OTHERWISE SPECIFIED		FCI		title		AirMax VS2 R.A. HEADER		3 Pair, 72 pos, 2mm, 8 Col		
linear		0.X		±.3		0.XX		±.10		
angular		0°		±2°		0.XXX		±.050		
www.fci.com		PDS: Rev :D		STATUS:Released		Printed: Feb 06, 2015		sheet 1 of 3		



RECOMMENDED PCB LAYOUT
FOR DIFFERENTIAL APPLICATIONS
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 8 & 12

SCALE 10:1

spec ref		---		dr		Lin-Soe Ngwe		2013/02/19		projection		MM		size		A2		scale		8:1			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Jackie Chen		2015/02/03						ecn no		ELX-DG-20160-1							
ASME Y14.5M				chr		-		-						rel level		Released							
				appr		Collins Lu		2015/02/06		product family		AirMax VSE											
surface 		linear				title		AirMax VS2 R.A. HEADER		dwg no		10124408		rev		D							
																						3 Pair, 72 pos, 2mm, 8 Col	
		0.X ±.3																					
		0.XX ±.10																					
		0.XXX ±.050																					
		angular		0° ±2°		www.fci.com		cat. no.		-		Product-		Customer Drw		sheet 2 of 3							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10124408-101LF](#) [10124408-111LF](#)