


## NOTES:

- MATERIALS AND FINISHES:  
BODY - BRASS, NICKEL PLATING  
BAYONET - ZINC DIECAST, NICKEL PLATING  
CONTACT - BRASS, GOLD PLATING  
INSULATOR - DELRIN
- ELECTRICAL:  
A. IMPEDANCE: 50 OHM  
B. FREQUENCY RANGE: DC 0-4 GHz  
C. VSWR(RETURN LOSS): 1.5 MAX.
- MECHANICAL:  
A. DURABILITY: 500 CYCLES MIN.  
B. TEMPERATURE RANGE: - 65°C to +165°C
- CRIMPED FERRULE  
HEX CRIMP SIZE .255"
- CONTACT PIN TO SOLDER

31-6005-RFX

## REVISIONS

PART NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	B	BAYONET WAS BRASS	7/13/06	46154	GH



## CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°	MATERIAL	DRAWN GARRA	DATE 23-Jun-06	TITLE BNC R/A CRIMP PLUG (FOR BELDEN RG-8/X, TIMES LMR-240MA)	Amphenol RF Danbury CT USA, Tainan Taiwan, Shenzhen China www.amphenolrf.com
		ENGINEER	DATE 23-Jun-06		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE	APPROVED F. Garra	DATE 7/13/06	SCALE: 3/1	SHEET 2 OF 2
		CAD FILE	F:\DWG\B\1112B4\8X-50\ND3GSZ	DWG SIZE B	CODE ID 74868
FINISH				REV B	ITEM NO. 01112ABB89ND5F
					PART NO. 31-6005-RFX

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[031-6005-RFX](#)