

PRODUCT NUMBER
76745-YXX-XXLF

- RoHS COMPATIBLE, SEE NOTE 8
- TOTAL NB OF POS (04 TO 72 POS)
- OPTION LETTER, SEE NOTE 6
- PIN STYLE

PLATING



- 1 = 0.76µm GOLD/GXT,
- 3 = 2µm MIN MATTE TIN FULL PLATED
- 5 / 8 = 0.38µm GOLD/GXT
- 1.27µm Ni MIN UNDERPLATING

NOTES:


- HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK.
- PIN MATERIAL : PHOSPHOR BRONZE.
- 12N MIN RETENTION IN EITHER DIRECTION.
- TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS PER ROW, $N \times 2.54 = 20.32\text{mm}$
- FOR STANDARD SELECTIVE GOLD PLATED PRODUCTS SEE DRAWINGS 54111 & 54121.
- OPTION LETTER :
 - = STANDARD PACKAGING IN POLYBAG
 - V = POLYBAGS PACKAGING FOR CUSTOMER DEDICATED PART
 - B = TUBE WITH PICK UP CAP AS AVAILABLE
- RETENTION IS APPLIED TO TWO ADJACENT PINS AT EACH END OF THE PRODUCT SEE SCHEMA 1
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE

8. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

- PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
- MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR WITH A 1.6mm MIN THICK CIRCUIT BOARD.
- LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- LEGAL STATEMENT: SEE GS-47-0004



SCHEMA 1
TWO RETENTION PIN AT EACH
END OF THE PRODUCT




OAL (OVERALL LENGTH)
REF

STACK HEIGHT

NOTE 3

DIM "B"



RECOMMENDED HOLE PATTERN

mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 	product family BSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified					title			
FF	B-19782	AMA	14.12.18	angles	linear	x.X ±0.3			HEADER STR,DR DOUBLE BODY			
FG	B-20322	AMA	15.01.27			x.XX ±0.13						
FH	F-22479	BVE	15.11.12			x.XXX ±0.05						
				dr	NIZZI P		94.05.05		dwg no		sheet 1 of 4	size
FC	B-17321	LMU	14.03.27	enrg	COMPAGNON J		95.12.05		76745		A3	
FD	B-19264	LMU	14.11.03	chr								
FE	B-19345	LMU	14.11.07	appd	JMC		95.12.05		type		CUSTOMER	Drawing
sheet	revision	FH	CB	F	A							
index	sheet	1	2	3	4							



FCIconnect.com

Copyright FCI

form: A3

APPLICATION SPECIFIC

PIN STYLE	MATING LENGTH ±0.2	STACK HEIGHT ±0.25	"B" ±0.25	("OAL") REF
01	8.71	19.76	2.65	31.12
02	6.87	16.5	3.05	26.42
03	6.87	13.0	3.63	23.5
04	5.6	6.5	2.88	14.98
05	5.51	8.0	3.05	16.56
06	6.61	11.3	3.05	20.96
07	5.58	10.3	2.54	18.42
08	5.81	7.7	3.05	16.56
09	5.72	5.08	2.54	13.34
10	6.9	10.45	2.71	20.06
11	11.2	9.5	2.8	23.5
13	9.07	6.3	3.05	18.42
14	5.33	21.5	2.48	29.31
17	7.5	23.45	3.05	34.0
19	9.5	10.45	3.55	23.5
21	11.96	18.5	3.2	33.66
23	9.0	25.9	3.05	37.95
24	8.87	14.5	3.05	26.42
25	9.84	11.43	9.85	31.12
28	6.6	8.25	2.8	17.65
29	9.1	15.7	3.2	28.0
34	8.0	12.0	3.0	23.0
36	10.55	7.5	10.53	28.58
40	7.0	6.5	3.06	16.56
55	13.0	20.0	3.2	36.2
57	11.78	5.08	3.23	20.06
58	23.0	8.5	5.5	36.97
59	9.0	18.2	9.0	36.2
62	9.2	9.3	3.5	22.0
68	6.75	8.0	2.9	17.65
71	6.8	5.2	2.69	14.69
79	9.95	39.0	3.05	52.0
80	5.68	7.0	2.3	15.0
88	10.8	8.0	3.7	22.5
AN	10.0	29.0	3.0	42.0
BD	11.7	13.5	3.21	28.41
BM	11.5	11.5	3.04	26.04
BT	8.5	35.0	8.5	52.0
CB	9.0	30.0	3.0	42.0
CD	9.24	12.0	9.24	30.48

SEE SHEET 3

APPLICATION SPECIFIC

PIN STYLE	MATING LENGTH ±0.2	STACK HEIGHT ±0.25	"B" ±0.25	("OAL") REF
CF	8.25	16.0	8.25	32.5
CG	6.0	40.0	6.0	52.0
CH	11.02	12.0	3.02	26.04
CN	7.08	5.60	7.08	19.77
CP	9.50	7.00	2.41	18.91
CT	11.0	6.0	11.0	28.0
CU	9.75	13.0	9.75	32.5
CV	9.44	13.00	3.60	26.04
CW	5.00	36.00	5.00	46.00
CX	10.00	26.00	6.00	42.00
CY	10.9	18.20	10.9	40.00
CZ	5.5	23.00	5.50	34.00
DA	13.00	14.50	6.50	34.00
DB	12.75	8.50	12.75	34.00
DC	SEE SHEET 3			
DE	6.00	34.00	6.00	46.00
DF	9.12	7.80	9.12	26.04
DG	3.50	43.00	3.50	50.00
DH	6.50	8.00	6.50	21.00
DJ	5.80	17.75	5.80	29.31
DK	5.40	9.00	2.90	17.30
DL	9.00	8.50	6.00	23.50
DM	7.40	23.70	3.30	34.40
DN	7.40	12.10	3.30	22.80
DP	8.00	16.80	5.40	30.20
DR	6.40	15.00	6.40	27.80
DS	7.00	29.00	7.00	43.00
DT	9.80	27.40	9.80	47.00
DU	9.50	36.50	9.50	55.50
DV	9.30	6.30	5.80	22.00
DW	5.30	40.40	3.30	49.00

SEE SHEET 3

SEE SHEET 3

SEE SHEET 3

APPLICATION SPECIFIC


PIN STYLE	MATING LENGTH ±0.2	STACK HEIGHT ±0.25	"B" ±0.25	("OAL") REF
DX	6.50	12.50	6.50	25.50
DY	6.50	9.50	6.50	22.50
EA	6.65	32.30	3.05	42.00
EB	2.66	15.00	5.84	23.50
EC	10.00	39.60	2.40	52.00
ED	5.40	57.20	2.40	65.00
EF	5.84	46.50	3.05	55.40
EG	5.60	20.00	5.64	31.24
EH	4.60	15.00	1.50	21.10
EJ	9.26	5.08	9.26	23.60
EK	6.00	7.50	6.00	19.50
EL	6.00	12.30	4.10	22.40

mat'l. code				surface	tolerance	projection	product family			
				ISO 1302	ISO 406 ISO 1101		BSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
CB	B-20322	AMA	15.01.27	angles	linear		HEADER STR,DR			
BV	F10-0259	LMU	10.12.19			scale	DOUBLE BODY			
BW	F11-0045	LMU	11.04.04	dr	COMPAGNON J	94.05.05	dwg no		sheet 2 of 4	size
BX	F12-0090	JFA	12.12.07	enrg	JMC	95.08.28	76745		A3	
BY	B-16665	LMU	14.01.06	chr			type		CUSTOMER	Drawing
CA	B-1345	LMU	14.11.07	appd	JMC	95.08.28				
sheet index	revision sheet									



FCIconnect.com

Copyright FCI



SPECIFICS PLATING AREA FOR PART NUMBERS :

P/N 76745-1CH-10LF

P/N 76745-1CH-18LF

P/N 76745-579R24LF

P/N 76745-579R30LF

P/N 76745-1CU-20LF

P/N 76745-1DF-26LF

AREA "A" & "B" : GOLD/GXT PLATING AREA

mat'l. code				surface ISO 1302 ☒ ISO 406 ISO 1101		tolerance ISO 406 ISO 1101		projection 		product family BSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
A	F06-110	LMU	06.01.26	angles	linear					HEADER STR,DR DOUBLE BODY			
B	F06-0196	LMU	06.06.20										
C	F07-0266	J.CO	07.10.15					scale					
D	F12-0023	LMU	12.06.06	dr	L.MULIN	06.01.31				dwg no		sheet 3 of 4	size
E	F12-0090	JFA	12.12.07	enr	J.COMPAGNON	06.01.31				76745		A3	
F	B-16665	LMU	14..01.06	chr									
				appd	JMC	06.01.31				type		CUSTOMER	Drawing
sheet index	revision sheet												



SPECIFIC PRODUCT NUMBER

76745-3DCA04LF

— RoHS COMPLIANT
 — TOTAL NB OF POS
 — PACKAGING TYPE, SEE NOTE 1
 — PIN STYLE
 — PLATING
 3 = 2µm MATTE TIN
 OVER 1.27µm Ni MIN

NOTES :

1. PACKAGING : A = TAPE & REEL PACKAGING
WITH PICK UP CAP INSTALLED
SEE TA 840
2. PRODUCT COMPATIBLE WITH REFLOW PROCESS.
255°C PEAK TEMPERATURE 10-40 SECONDES IN
A CONVECTION, INFRA-RED OR VAPOR PHASE



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BSTIK									
ltr	ecn no	dr	date	tolerances unless otherwise specified						title									
A	B-16665	LMU	14.01.06	angles		linear				HEADER STR,DR									
								mm		DOUBLE BODY									
								scale											
				dr		L.MULIN		13.02.18		dwg no sheet 4 of 4 size 76745 A3									
				enrg		J.COMPAGNON		13.02.18											
				chr															
				appd		JMC		13.02.18		FCJ type CUSTOMER Drawing									
sheet index		revision sheet																	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

[76745-159-50LF](#) [76745-823-72LF](#) [76745-1CT-06LF](#) [76745-8DH-08LF](#) [76745-8AN-26LF](#) [76745-101-44LF](#) [76745-104-28LF](#) [76745-109-72LF](#) [76745-110-72LF](#) [76745-113-18LF](#) [76745-171-20LF](#) [76745-1CH-10LF](#) [76745-1CH-18LF](#) [76745-1CN-20LF](#) [76745-1CP-20LF](#) [76745-1CP-22LF](#) [76745-321-10LF](#) [76745-321-14LF](#) [76745-323-72LF](#) [76745-501-12LF](#) [76745-106-06LF](#) [76745-106-20LF](#) [76745-106-40LF](#) [76745-117-40LF](#) [76745-121-10LF](#) [76745-121-14LF](#) [76745-124-18LF](#) [76745-129-72LF](#) [76745-136-48LF](#) [76745-140-36LF](#) [76745-140-38LF](#) [76745-157-26LF](#) [76745-168-60LF](#) [76745-1BT-36LF](#) [76745-1CD-40LF](#) [76745-1CF-24LF](#) [76745-1CV-24LF](#) [76745-1CW-10LF](#) [76745-1CY-50LF](#) [76745-1DA-28LF](#) [76745-304-72LF](#) [76745-325-18LF](#) [76745-507-72LF](#) [76745-558-64LF](#) [76745-579R24LF](#) [76745-579R30LF](#) [76745-580-20LF](#) [76745-809-12LF](#) [76745-8DJ-24LF](#) [76745-8DJ-32LF](#) [76745-128-40LF](#) [76745-1DL-06LF](#) [76745-8DP-10LF](#) [76745-113-22LF](#) [76745-1DV-12LF](#) [76745-1DP-10LF](#) [76745-1CZ-20LF](#) [76745-128-72LF](#) [76745-8CF-10LF](#) [76745-157-22LF](#) [76745-124-36LF](#) [76745-1DT-12LF](#) [76745-8DK-32LF](#) [76745-1DA-32LF](#) [76745-102-14LF](#) [76745-105-06LF](#) [76745-1DF-26LF](#) [76745-103-30LF](#) [76745-802-10LF](#) [76745-1CN-06LF](#) [76745-1CT-16LF](#) [76745-109-24LF](#) [76745-8DW-20LF](#) [76745-1CU-20LF](#) [76745-1CB-12LF](#) [76745-103-40LF](#) [76745-8DB-40LF](#) [76745-106-26LF](#) [76745-1CF-10LF](#) [76745-124-06LF](#) [76745-106-72LF](#) [76745-124-10LF](#) [76745-3EF-10LF](#) [76745-3EJ-06LF](#) [76745-3DT-52LF](#) [76745-162-06LF](#) [76745-155-04LF](#) [76745-1CN-08LF](#) [76745-1CB-24LF](#) [76745-3EF-28LF](#) [76745-134-12LF](#) [76745-514-20LF](#)