









TOTAL NUMBER OF POWER CONTACTS AND NUMBER OF SIGNAL CONTACTS	Dim"A"	DIM " B"
2P2S2P	13.0	3.30
2P4S2P	15.0	3.30
2P6S2P	17.0	3.30
2P8S2P	19.0	3.30
2P10S2P	21.0	3.30
2P12S2P	23.0	3.30
4P2S4P	21.4	3.30
4P4S4P	23.4	3.30
4P6S4P	25.4	3.30
4P8S4P	27.4	3.30
4P10S4P	29.4	3.30
4P12S4P	31.4	3.30
6P2S6P	29.8	3.30
6P4S6P	31.8	3.30
6P6S6P	33.8	3.30
6P8S6P	35.8	3.30
6P10S6P	37.8	3.30
6P12S6P	39.8	3.60
8P2S8P	38.2	3.60
8P4S8P	40.2	3.60
8P6S8P	42.2	3.60
8P8S8P	44.2	3.60
8P10S8P	46.2	3.60
8P12S8P	48.2	3.60
2POS0P(2P)	5.0	3.30
2POS2P(4P)	9.6	3.30
2POS4P(6P)	13.8	3.30
4POS4P(8P)	18.0	3.30
4POS6P(10P)	22.2	3.30
6POS6P(12P)	26.4	3.30
6POS8P(14P)	30.6	3.30
8POS8P(16P)	34.8	3.30


spec ref			dr		Jes Wu	2015/02/16	projection		MM		size	A2		scale		5:1								
tolerance std			eng			Jes Wu	2015/03/25					ecn no		-										
ISO 406			chr			-	-					rel level		Preliminary										
ISO 1101			appr			-	-					-		-										
TOLERANCES UNLESS OTHERWISE SPECIFIED			surface		linear		0.X ±0.50		0.XX ±0.25		0.XXX ±0.10		angular 0° ±3°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 1 of 2	
ISO 1302			FCi		title		Minithek Pwr Hybrid 4.2mm		dwg no		10129815		rev		1									
ISO 1302			REC HSG ASSY		-		-		-		-		-		-									




2POS0P(2P)




8POS8P(16P)




6P2S6P




2POS2P(4P)




6POS8P(14P)




2POS4P(6P)



6POS6P(12P)



4POS4P(8P)



4POS6P(10P)

POWER PIN LAYOUT (WITH OR WITHOUT SIGNAL PINS)

10129815 - X X X X X LF

BASE NUMBER

LEAD FREE

RESERVE NUMBER: 00

NUMBER OF RIGHT POWER PINS : 0,2,4,6,8

NUMBER OF SIGNAL PINS : 0,2,4,6,8,A-10,B-12

NUMBER OF LEFT POWER PINS :2,4,6,8



NOTES:

1. MATERIALS:
NYLON 6/6 , UL94V-0, COLOR: NATURE

3. PRODUCT SPECIFICATION: GS-12-1288.

4. APPLICATION SPECIFICATION: GS-20-0438.

5. PACKAGING SPECIFICATION: GS-14-2450.

spec ref				dr		Jes Wu	2015/02/16	projection		MM		size		A2	scale		5:1						
tolerance std				eng		Jes Wu	2015/03/25					ecn no - rel level Preliminary											
ISO 406				chr		-	-																
ISO 1101				appr		-	-																
TOLERANCES UNLESS OTHERWISE SPECIFIED																							
surface				linear		0.X		±0.50				title		Minitex Pwr Hybrid 4.2mm		dwg no		10129815		rev		1	
ISO 1302				0.XX		±0.25																	
				0.XXX		±0.10																	
angular				0°		±3°		www.fci.com		cat. no.		-		Product - Customer Drw				sheet 2 of 2					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10129815-22200LF](#) [10129815-44400LF](#) [10129815-84800LF](#) [10129815-80800LF](#) [10129815-64600LF](#) [10129815-86800LF](#) [10129815-88800LF](#) [10129815-66600LF](#) [10129815-24200LF](#)