






NOTES:

1. MATERIALS AND FINISHES:
BODY - BRASS, GOLD PLATING
CONTACT - BeCu, GOLD PLATING
INSULATOR - PTFE
2. ELECTRICAL:
A. IMPEDANCE: 75 OHMS
B. FREQUENCY RANGE: DC - 4 GHz
C. RETURN LOSS : 30 dB @ 3 GHz
D. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
E. INSULATION RESISTANCE: 10,000 MEGOHMS MIN
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
4. ENVIRONMENTAL:
A. THERMAL SHOCK PER MIL-STD-202 METHOD 107
TEST CONDITION B (EXCEPT HIGH TEMP @200°C)
B. VIBRATION: MIL-STD-202 METHOD 204 TEST CONDITION B
C. SHOCK: MIL-STD-202 METHOD 213 TEST CONDITION B
D. CORROSION: MIL-STD-202 METHOD 101
TEST CONDITION B 5% SALT SOLUTION
5. AMPHENOL SPANNER WRENCH 227-1490 REQUIRED TO MOUNT CONNECTOR TO PANEL.
6. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOLRF, 34-1018 AND DATE CODE"




THIRD ANGLE PROJ.



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY


UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL SEE NOTES	DRAWN STAR	DATE 25-May-16	TITLE HD BNC BHD JACK EDGE MOUNT FOR 0.062" THICK BOARD		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER PADMANABHAN E	DATE 27-Jan-10				
	REFERENCE EAR # 3896	APPROVED S.HSIEH	DATE 25-May-16	SCALE: 9.0:1.0		SHEET	2 OF 5
	CONFIGURATION LEVEL:	CAD FILE	DWG SIZE B		REV C		
	FINISH						

THIRD ANGLE PROJ. 		REVISIONS			
REV	DESCRIPTION	DATE	ECO	APPR	
A	RELEASED TO MFG.	--	48167	AAP	
B	UNDERCUT REMOVED\RD-DM12071801R3	26-Jul-12	49164	SH	
C	UPDATED INTERFACE \RD-DM16052301S7	25-May-16	00843	MJD	

CONFIGURATION - 0

RECOMMENDED PCB LAUNCH FOR OPTIMAL RF PERFORMANCE

VARIATIONS IN BOARD SUBSTRATE AND TRACE MAY REQUIRE DIFFERENT GEOMETRY




<div>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°</div> <div>NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.</div>	MATERIAL -		DRAWN STAR	DATE 25-May-16	TITLE HD BNC BHD JACK EDGE MOUNT FOR 0.062" THICK BOARD		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
	REFERENCE EAR # 3896		ENGINEER PADMANABHAN E	DATE 25-Jun-10				
	CONFIGURATION LEVEL:		APPROVED S.HSIEH	DATE 25-May-16	SCALE: 12.0:1.0	SHEET 3 OF 5	DRAWING NO. 34-1018	
	FINISH		CAD FILE		DWG SIZE B	REV C	ITEM NO. 34-1018 PART NO. 34-1018	

THIRD ANGLE PROJ.		REVISIONS			
REV	DESCRIPTION	DATE	ECO	APPR	
A	RELEASED TO MFG.		48167	PNE	
B	UNDERCUT REMOVED\RD-DM12071801R3	26-Jul-12	49164	SH	
C	UPDATED INTERFACE \RD-DM16052301S7	25-May-16	00843	MJD	

CONFIGURATION - 1

RECOMMENDED PCB LAUNCH FOR OPTIMAL RF PERFORMANCE

VARIATIONS IN BOARD SUBSTRATE AND TRACE MAY REQUIRE DIFFERENT GEOMETRY




<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°</p> <p>NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.</p>	MATERIAL -		DRAWN STAR	DATE 25-May-16	TITLE HD BNC BHD JACK EDGE MOUNT FOR 0.062" THICK BOARD		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
	REFERENCE EAR # 3896		ENGINEER PADMANABHAN E	DATE 15-Jul-10				
	CONFIGURATION LEVEL:		APPROVED S.HSIEH	DATE 25-May-16	SCALE: 6.0:1.0	SHEET 4 OF 5	DRAWING NO. 34-1018	
	FINISH		CAD FILE		DWG SIZE B	REV C	ITEM NO. 34-1018 PART NO. 34-1018	

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASED TO MFG.	--	48167	PNE
B	UNDERCUT REMOVED\RD-DM12071801R3	26-Jul-12	49164	SH
C	UPDATED INTERFACE \RD-DM16052301S7	25-May-16	00843	MJD



RECOMMENDED PCB LAUNCH



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ± 0.1mm ± 0.2mm ± 0.3mm ± 1°	MATERIAL - -	DRAWN STAR	DATE 25-May-16	TITLE HD BNC BHD JACK EDGE MOUNT FOR 0.062" THICK BOARD		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE EAR # 3896	APPROVED S.HSIEH	DATE 25-May-16	SCALE: 4.0:1.0 SHEET 5 OF 5		DRAWING NO. 34-1018	
	CONFIGURATION LEVEL:	CAD FILE	DWG SIZE B		REV C	ITEM NO. 34-1018	
	FINISH					PART NO. 34-1018	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[34-1018](#) [034-1018](#)