

NOTES:

1. MATERIALS AND FINISHES:

BODY, BAYONET SLEEVE
RETAINING RING & WASHER - BRASS, NICKEL PLATING
OUTER CONTACT - BeCu, NICKEL PLATING
CONTACT - PHOSPHOR BRONZE, GOLD PLATING
BULLET CONTACT - BRASS, GOLD PLATING
FERRULE - COPPER, NICKEL PLATING
INSULATOR - PTFE, NATURAL
SPRING - STAINLESS STEEL, PASSIVATED
GASKET - FLUOROSILICONE, BLUE

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 6 GHz
C. RETURN LOSS : 30dB MIN
D. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.
E. INSULATION RESISTANCE: 10,000 MΩ MIN

3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65°C TO +165°C

4. ENVIRONMENTAL:

A. THERMAL SHOCK PER MIL-STD-202 METHOD 107
TEST CONDITION B (EXCEPT HIGH TEMP @200°C)
B. VIBRATION: MIL-STD-202 METHOD 204 TEST CONDITION B
C. SHOCK: MIL-STD-202 METHOD 213 TEST CONDITION B
D. CORROSION: MIL-STD-202 METHOD 101
TEST CONDITION B 5% SALT SOLUTION

5. PACKAGING:

A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED:
"AMPHENOL RF, 34-5011 DATE CODE
U.S. PATENT NO. 7,553,177"

6. HIGH DENSITY INSTALLATION/REMOVAL TOOL: 227-T2000

7. CABLE ASSEMBLY INSTRUCTIONS:


A. TRIM CABLE AS SHOWN.
B. SLIDE FERRULE ONTO THE CABLE.
C. SOLDER BULLET CONTACT TO CABLE CENTER CONDUCTOR
D. CRIMP FERRULE WITH 0.105" HEX.

8 SHOWS CABLE ENTRY DIMENSIONS.


THIRD ANGLE PROJ.

REVISIONS


REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	05-Apr-13	49282	AAP
B	OPTIMIZED CRIMP DESIGN	23-Oct-17	05587	SS/VK
C	UPDATE THE BACK-END DESIGN ON DIAMOND KNURL	26-Feb-18	07068	SS



RECOMMENDED CABLE STRIPPING DIMENSIONS



SCALE 3.500



PROTECTED UNDER U.S. PATENT # 7,553,177

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
<0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL SEE NOTES	DRAWN K. SONG DATE 01-Mar-18	TITLE 50 OHM HD-BNC STR PLUG FOR RG 178 CABLE SCALE: 10.0:1.0 SHEET 2 OF 2 DWG SIZE B	REV C	Amphenol RF www.amphenolrf.com DRAWING NO. 34-5011 ITEM NO. 34-5011 PART NO. 34-5011
REFERENCE EAR # 4505 & EAR # 7188	ENGINEER A ARUN PRABU DATE 09-May-11			
CONFIGURATION LEVEL: In Work	APPROVED S. HSIEH DATE 01-Mar-18			
FINISH	CAD FILE			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[034-5011](#)