




- NOTES:
- 1. MATERIALS AND FINISHES:(PLATING THICKNESS IN MICRO-INCHES)
BODY - BRASS, NICKEL PLATING
CONTACT PIN - BERYLLIUM COPPER, SILVER PLATING
INSULATOR - PTFE,NATURAL
 - 2. ELECTRICAL:
 - A. IMPEDANCE: 50 OHM
 - B. FREQUENCY RANGE: DC - 4 GHz
 - C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
 - 3. MECHANICAL:
 - A. DURABILITY: 500 CYCLES MIN.
 - B. TEMPERATURE RANGE: -65° C TO +165° C

THIRD ANGLE PROJ.		REVISIONS			
REV	DESCRIPTION	DATE	ECO	APPR	
A	RELEASE TO MFG.	5/17/63	8607		
T	STAMP "AMPHENOL" WAS "74868"\RD-DM12092001R3	19-Oct-12	49076	SH	



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implicatioin or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN R. MAO	DATE 18-Jun-12	TITLE BNC JACK TO JACK PANEL MOUNTED ADAPTOR		Amphenol RF www.amphenolrf.com	
		ENGINEER D. ROYCE	DATE 10/19/92				
	REFERENCE	APPROVED S. HSIEH	DATE 15-Jun-12	SCALE: 4.0:1.0 SHEET 2 OF 2		DRAWING NO. 47000	
	CONFIGURATION LEVEL: □□□□	CAD FILE		DWG SIZE B	REV T	ITEM NO. 47000	
	FINISH					PART NO. 47000	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[47000](#) [000-47000](#)