



SIGN	DATE	DESCRIPTION	APPROVER
△	4/01'09	Current, wire range, torque, safety approval are changed	Jody
△	11/17'09	Wire guard solder pin is changed from Brass to Copper	Aaron
△	04/04'11	Add is spec.	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

#### Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Coamp : Steel stamping , Zinc plated
- △ ● Item 3 Wire guard solder pin : Copper , Tin plated
- Item 4 Terminal screw: Steel Zinc plating"- "slot type

- Electrical cULs IEC
- Voltage rating : 600V 1000V
  - △ ● Current rating : 65A 76A
  - Wire range : 16.00mm<sup>2</sup>
  - Solid wire (AWG) : 6-20
  - Stranded wire (AWG) : 6-20
  - △ ● Torque (LB.-In.) : 19LB-In
  - Screw : M4.5
  - Wire strip length : 10-11mm
  - Withstanding voltage : 2.2KV 6KV
  - Operating temperature : -40°C+115°C
  - Soldering temperature : 250°C+10°C/5 Sec
  - Safety Approval : cULus

VP xx 85 x 7 xxxx G

NO of poles

- 02 2 CONTACTS 0: Black  
03 3 CONTACTS 5: Green (RAL 6018/T)  
... .. 6: Blue  
12 12 CONTACTS 8: Grey (RAL 7035/D)

RoHS  
Pb<40,000ppm

0000 Standard @ Logo  
000A Standard ANY Logo  
Any special item by  
customer request,  
please contact sales  
department.

Poles	02	03	04	05	06	07	08	09	10	11	12
Dim L	25.40	38.10	50.80	63.50	76.20	88.90	101.60	114.30	127.0	139.70	152.40
Dim B	12.70	25.40	38.10	50.80	63.50	76.20	88.90	101.60	114.30	127.0	139.70
TOL	±0.15				±0.20				±0.30		

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VP 12.70 Series ( Double tail 0.9x1.0 ) Contacts Pin Pitch 4.0mm			
PART NO.	VPxx85x7xxxxG			DWG NO.	8VP0105
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
			Chen Bo 2011.04.04		Tolerance
					X. ±0.50
					X.X ±0.30
				SHEET: 01/01	X.XX ±0.10
				REV.: E	X° ±1°

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[VP0285870000G](#) [VP0385870000G](#) [VP0485870000G](#) [VP0585870000G](#) [VP0685870000G](#) [VP0785870000G](#)  
[VP0885870000G](#) [VP0985870000G](#) [VP1085870000G](#) [VP1185870000G](#) [VP1285870000G](#)