




1. MATERIALS AND FINISHES:
 - BODY - BRASS, NICKEL PLATED
 - CONTACT - BeCu, SILVER PLATED
 - INSULATOR - PTFE, NATURAL
2. ELECTRICAL:
 - A. IMPEDANCE: 50 OHM
 - B. FREQUENCY RANGE: DC 0-11 GHz
 - C. DIELECTRIC WITHSTANDING VOLTAGE: 2500 VRMS, MIN.
3. MECHANICAL:
 - A. DURABILITY: 500 CYCLES MIN.
 - B. TEMPERATURE RANGE: -65° C TO+165° C

REVISIONS


REV	DESCRIPTION	DATE	ECO	APPR
AD	REDRAWN TO UPDATE FORMAT/RD-DM10031001T1	17-Mar-10		SH
AE	STAMP "AMPHENOL " WAS "74868 " \RD-DM12040501R3	19-Apr-12	48877	DH



RECOMMENDED MOUNTING HOLE DIMENSIONS



SCALE 1.600



ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ± 0.1mm ± 0.2mm ± 0.3mm ± 1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN T.DENG	DATE 27-Feb-10	TITLE RECEPTACLE TYPE 'N' UG-58 A/U		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER C.WANG	DATE 27-Feb-10				
	REFERENCE	APPROVED S.HSIEH	DATE 17-Mar-10	SCALE: 3.9:1.0	SHEET 2 OF 2	DRAWING NO. 82-97	
		CAD FILE		DWG SIZE B		REV AE	ITEM NO. 82-97
	FINISH		I: /N/82-97				PART NO. 82-97

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[82-97](#) [082-97](#)