



1. MATERIALS AND FINISHES:
RP TNC STR BHD JACK IP 67 - BRASS, ELECTROLESS NICKEL PLATING
AMC RA PLUG:
HOUSING - PBT, BLACK
CONTACT & GROUND CONTACT - PHOSPHOR BRONZE, GOLD PLATING
CABLE - 1.13 MM CABLE
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
3. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-850-263-XXX AND DATE CODE"


A technical drawing of a cable tie-inlet. It features a threaded base with a flange, a central cable passage, and a cable tie-inlet. A cable is shown passing through the central passage and secured by the cable tie-inlet.

RECOMMENDED MOUNTING HOLE DIMENSIONS



| LENGTH TABLE | |
|---------------------------|--|
| PART NUMBER (IMPERIAL) | LENGTH AND TOLERANCE 'L' IN MM (INCHES) |
| 95-850-263-050 | 50.00 ± 3.81 [1.969 ± 0.150] |
| 95-850-263-100 | 100.00 ± 3.81 [3.937 ± 0.150] |
| 95-850-263-150 | 150.00 ± 3.81 [5.906 ± 0.150] |
| 95-850-263-200 | 200.00 ± 5.08 [7.874 ± 0.200] |
| 95-850-263-250 | 250.00 ± 5.08 [9.843 ± 0.200] |
| 95-850-263-300 | 300.00 ± 5.08 [11.811 ± 0.200] |

| | |
|---|--|
| <input checked="" type="checkbox"/> FREQUENCY: DC - 6 GHz | <input checked="" type="checkbox"/> CONTINUITY |
| <input type="checkbox"/> VSWR: ____ MAX. | <input checked="" type="checkbox"/> HI-POT: 200 VRMS |
| <input type="checkbox"/> INS. LOSS: ____ dB MAX. | <input type="checkbox"/> OTHER: |

| | | | | | | | | | | | | | | | | | | | | | | | | | | |
|--|--|--|--|--|--|---------------------------|--|---|--|---|--|-----------|--|---------------|-------------------------|-----------------------|--|-------------------|--|------------------|--|----------------|--|-------------------------|----------------------------|--------------|
| NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data. | | | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC [INCHES] AND TOLERANCES ARE: <0.5mm = ±0.05mm [$<0.020 = \pm 0.002$] >0.5 - 6mm = ±0.1mm [$>0.020 - 0.236 = \pm 0.004$] >6.00 - 30mm = ±0.2mm [$>0.236 - 1.181 = \pm 0.008$] >30.00 - 120mm = ±0.3mm [$>1.181 - 4.725 = \pm 0.012$] ----- ANGLES = ±1° | | | MATERIAL SEE NOTES | | TITLE RP TNC STR BHD JACK IP 67 TO AMC RA PLUG USING 1.13 MM CABLE VARIOUS LENGTH | | Amphenol RF | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | THIRD ANGLE PROJ.  | | REFERENCE | | EAR# 10475 | | ENGINEER VIJAY N M | | DATE 03-FEB-21 | | SHEET NO. 2 OF 2 | | SCALE: 4.0:1.0 | | SIZE | DRAWING NO. 95-850-263-XXX | REV A |
| | | | | | | | | | | | | | | | | | | | | | | | | ITEM NO. 95-850-263-XXX | | |
| | | | | | | | | | | | | | | B | PART NO. 95-850-263-XXX | | | | | | | | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[095-850-263-050](#) [095-850-263-100](#) [095-850-263-150](#) [095-850-263-200](#) [095-850-263-250](#) [095-850-263-300](#)