


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

| REV. | DESCRIPTION | REVISIONS | DATE | APPROVED |
|------|-------------|-----------|------|----------|
| | | | | |



MATERIAL:

SMA: BODY: BRASS, GOLD-PLATED,
CENTER PIN: BRASS, GOLD-PLATED,

CABLE: RG316

THE TOLERANCE IS:

<1000 ±.5
>=1000 ±.10



| No. | ACD No. | L(mm) | TITLE |
|-----|---------------------|-------|---------------------------|
| 9 | CO-316SMAX200-010 | 3050 | CA SMA M/SMA M RG316 10' |
| 8 | CO-316SMAX200-007.5 | 2286 | CA SMA M/SMA M RG316 7.5' |
| 7 | CO-316SMAX200-005 | 1525 | CA SMA M/SMA M RG316 5' |
| 6 | CO-316SMAX200-004 | 1220 | CA SMA M/SMA M RG316 4' |
| 5 | CO-316SMAX200-003 | 915 | CA SMA M/SMA M RG316 3' |
| 4 | CO-316SMAX200-002.5 | 762 | CA SMA M/SMA M RG316 2.5' |
| 3 | CO-316SMAX200-002 | 610 | CA SMA M/SMA M RG316 2' |
| 2 | CO-316SMAX200-001.5 | 457 | CA SMA M/SMA M RG316 1.5' |
| 1 | CO-316SMAX200-001 | 305 | CA SMA M/SMA M RG316 1' |

UNLESS OTHERWISE SPECIFIED EAR N.D.
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

| DECIMALS | ANGLES | APPROVALS | DATE |
|------------|--------|----------------|------------|
| .X ±.X | ± X° | DESIGN/INHOUSE | 2006-11-18 |
| .XX ±.XX | | CHECKED | |
| .XXX ±.XXX | | RESP ENG | |

THIRD ANGLE PROJECTION



WFG ENG

RG 316/U TWO IN-LINE
SMA PLUGS

SIZE DWG. NO.
A CO-316SMAX200-XXX

REV.

NOTES: UNLESS OTHERWISE SPECIFIED

CAD FILE:

SCALE

SHEET

OF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CO-316SMAX200-003](#) [CO-316SMAX200-005](#) [CO-316SMAX200-001](#) [CO-316SMAX200-002](#) [CO-316SMAX200-004](#)
[CO-316SMAX200-007.5](#) [CO-316SMAX200-010](#)