



Dimension

A	$N \times 5.08 + 1.0$
B	$(N-1) \times 5.08$

N=Number of poles

	TOL			
	2p-6p	7p-12p	13p-18p	19p-24p
A	±0.10	±0.15	±0.20	±0.30
B	±0.10	±0.15	±0.20	±0.30

△ PCB Layout

SIGN	DATE	DESCRIPTION	APPROVER
△	11/19'07	PCB Layout changed	Tony
△	05/30'11	Wire strip length is changed from 6-7mm to 5-6mm	Steven
△	05/30'11	Add "cULus" Safety Approval logo	Steven
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item① Terminal side housing: Thermoplastic (UL94V-0)
- Item② Terminal housing: Thermoplastic (UL94V-0)
- Item③ Terminal cover: Thermoplastic (UL94V-0)
- Item④ Spring clamp: Stainless steel
- Item⑤ Contact pin of short: Brass, Tin plated
- Item⑥ Contact pin of middle: Brass, Tin plated
- Item⑦ Contact pin of long: Brass, Tin plated

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- △ ● Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- △ ● Safety Approval: cULus
- Critical dimension: △

HR xx 3 0 x 0 xxxx G

No. OF POLES

03: 3x1 POLES

06: 3x2 POLES

69: 3x23 POLES

72: 3x24 POLES

COLOR

0: BLACK

5: GREEN (RAL 6018/T)

6: BLUE

8: GREY (RAL 7004/P)

G: Pb<40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HR 5.08mm Series (Solder pins in line)						
PART NO.	HRxx30x0xxxxG			DWG NO.	8HR0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Steven 2011.05.30	Tony 2007.11.19		Tolerance		
					UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
				SHEET: 01/01	REV.: D	X.XX	±0.10
						X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>HR0630800000G</u>	<u>HR0930800000G</u>	<u>HR1230800000G</u>	<u>HR1530800000G</u>	<u>HR1830800000G</u>	<u>HR2130800000G</u>
<u>HR2430800000G</u>	<u>HR2730800000G</u>	<u>HR3030800000G</u>	<u>HR3330800000G</u>	<u>HR3630800000G</u>	<u>HR3930800000G</u>
<u>HR4230800000G</u>	<u>HR4530800000G</u>	<u>HR4830800000G</u>	<u>HR5130800000G</u>	<u>HR5430800000G</u>	<u>HR5730800000G</u>
<u>HR6030800000G</u>	<u>HR6330800000G</u>	<u>HR6630800000G</u>	<u>HR6930800000G</u>	<u>HR7230800000G</u>	