





N = Number of poles
 Dim A = $N \times 5.0 + 0.50$
 Dim B = $(N - 1) \times 5.0$

	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.25	±0.25
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40



SIGN	DATE	DESCRIPTION	APPROVER
	11.01'05	Standard spec is changed.	Marivn
	8/07'06	Added VDE and TUV standard	梁仁松
	8/07'06	DWG NO. changed from 8TS0204 to 8TS0004	梁仁松
	12/02'08	With flange screw changed from "-" slot type to "+/-" slot type	Jacke
	12/02'08	The temperature changed from -30°C +105°C to -40°C +115°C	Jacke
	12/02'08	Add the tolerance table	Jacke
	2010.03.13	Add the 2p mark	Jacke
	2010.05.28	The design is changed	Chen Bo
	2010.08.16	The design is changed	Chen Bo

Material

- Item a Clamp: Brass(CuZn) Ni plated
- Item b Terminal screw: Steel Zinc plating "-" slot type
- Item c Female contact: PhBz Tin plated
- Item d Terminal (up body): Thermoplastic (UL94V-0)
- Item e Terminal (down body): Thermoplastic (UL94V-0)
- Item f With flange screw: Steel Zinc plating "+/-" slot type M2.5

Electrical cULus/VDE/TUV

- Voltage rating: 300VAC/300VAC/300VAC
- Current rating: 15A/17A/15A
- Wire range: 2.5mm² / 0.34-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5Lb-In./0.5Nm/0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval:

TS xx 71 x D xxxx G

RoHS
 Pb<40,000ppm

- 02 2 CONTACTS
- 03 3 CONTACTS
-
- 24 24 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

- 0000: "@" Logo
- 000A: "ANYTEK" Mark
- 0091: "ANYTEK" Mark
- Any special item by customer request.
- please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TS-5.0mm Series(W/latching hooks on the back side) With flange						
PART NO.	TSxx71xDxxxxG			DWG NO.	8TS0004		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
			Chen Bo 2010.08.16		UNIT: mm	Tolerance	
					SCALE: NONE	X. ±0.50	
						X.X ±0.30	
						X.XX ±0.10	
						X° ±1°	
				SHEET: 01/01	REV.: I		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>TS02715D0000G</u>	<u>TS03715D0000G</u>	<u>TS04715D0000G</u>	<u>TS05715D0000G</u>	<u>TS06715D0000G</u>	<u>TS07715D0000G</u>
<u>TS08715D0000G</u>	<u>TS09715D0000G</u>	<u>TS10715D0000G</u>	<u>TS11715D0000G</u>	<u>TS12715D0000G</u>	<u>TS13715D0000G</u>
<u>TS14715D0000G</u>	<u>TS15715D0000G</u>	<u>TS16715D0000G</u>	<u>TS17715D0000G</u>	<u>TS18715D0000G</u>	<u>TS19715D0000G</u>
<u>TS20715D0000G</u>	<u>TS21715D0000G</u>	<u>TS22715D0000G</u>	<u>TS23715D0000G</u>	<u>TS24715D0000G</u>	<u>TS08718D0000G</u>
<u>TS09710D0000G</u>	<u>TS06718D0000G</u>	<u>TS07710D0000G</u>	<u>TS09718D0000G</u>	<u>TS10718D0000G</u>	<u>TS03710D0000G</u>
<u>TS02718D0000G</u>	<u>TS04710D0000G</u>	<u>TS05710D0000G</u>	<u>TS05718D0000G</u>	<u>TS08710D0000G</u>	<u>TS07718D0000G</u>
<u>TS03718D0000G</u>	<u>TS13718D0000G</u>	<u>TS11718D0000G</u>	<u>TS12710D0000G</u>	<u>TS14718D0000G</u>	<u>TS18710D0000G</u>
<u>TS13710D0000G</u>	<u>TS14710D0000G</u>	<u>TS15710D0000G</u>	<u>TS11710D0000G</u>	<u>TS23710D0000G</u>	<u>TS16718D0000G</u>
<u>TS19710D0000G</u>	<u>TS20718D0000G</u>	<u>TS22710D0000G</u>	<u>TS21710D0000G</u>	<u>TS24710D0000G</u>	<u>TS15718D0000G</u>
<u>TS17710D0000G</u>	<u>TS23718D0000G</u>	<u>TS10710D0000G</u>	<u>TS21718D0000G</u>	<u>TS18718D0000G</u>	<u>TS24718D0000G</u>
<u>TS19718D0000G</u>	<u>TS22718D0000G</u>	<u>TS04718D0000G</u>	<u>TS06710D0000G</u>	<u>TS17718D0000G</u>	<u>TS02710D0000G</u>
<u>TS12718D0000G</u>	<u>TS16710D0000G</u>	<u>TS20710D0000G</u>			