








Technical drawing of a mechanical part, likely a valve or actuator component, showing dimensions in millimeters. The drawing includes a top view and a side view. The top view shows a circular feature with a diameter of 26.5 mm and a central rectangular section with a width of 23.5 mm. The side view shows a profile with a height of 10.5 mm and a base width of 12.5 mm. The drawing is labeled with '26.5', '23.5', '10.5', and '12.5'.



- ④ Screw Nut
- ③ Tooth Washer
- ② Gasket



Assembly Instruction




△ Note:

- *  Important Dimension.
- * Waterproof Rate: IP68
IP68: 1M depth of water in 24 Hrs.
(防水等級: IP68)
IP68: 水深一米測試24小時
- * Shell: Zinc Alloy ,Electrodeposition Coating ,Black.
- * Insulation: Nylon ,Black
- * Female Pin: Copper Alloy ,Gold Plated
- * Gasket: Silicone ,Gray
- * Recommended Panel Thickness 5.0mm(Max).

Recommend Panel Cut-Out

UNIT: mm



TOLERANCE	
.X	± 0.25
.XX	± 0.1
.XXX	± 0.05
ANGLES	$\pm 1^{\circ}$

TITLE

PANEL NUT 10PIN M CONN F PIN

SCALE C - E

SIZE	A4
------	----

WC-REV. 1 3

QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DESCRIPTION	QTY	UNIT PRICE	TOTAL
1	...	...	...	...
2	...	...	...	...
3	...	...	...	...
4	...	...	...	...
5	...	...	...	...
6	...	...	...	...
7	...	...	...	...
8	...	...	...	...
9	...	...	...	...
10	...	...	...	...
11	...	...	...	...
12	...	...	...	...
13	...	...	...	...
14	...	...	...	...
15	...	...	...	...
16	...	...	...	...
17	...	...	...	...
18	...	...	...	...
19	...	...	...	...
20	...	...	...	...
21	...	...	...	...
22	...	...	...	...
23	...	...	...	...
24	...	...	...	...
25	...	...	...	...
26	...	...	...	...
27	...	...	...	...
28	...	...	...	...
29	...	...	...	...
30	...	...	...	...
31	...	...	...	...
32	...	...	...	...
33	...	...	...	...
34	...	...	...	...
35	...	...	...	...
36	...	...	...	...
37	...	...	...	...
38	...	...	...	...
39	...	...	...	...
40	...	...	...	...
41	...	...	...	...
42	...	...	...	...
43	...	...	...	...
44	...	...	...	...
45	...	...	...	...
46	...	...	...	...
47	...	...	...	...
48	...	...	...	...
49	...	...	...	...
50	...	...	...	...
51	...	...	...	...
52	...	...	...	...
53	...	...	...	...
54	...	...	...	...
55	...	...	...	...
56	...	...	...	...
57	...	...	...	...
58	...	...	...	...
59	...	...	...	...
60	...	...	...	...
61	...	...	...	...
62	...	...	...	...
63	...	...	...	...
64	...	...	...	...
65	...	...	...	...
66	...	...	...	...
67	...	...	...	...
68	...	...	...	...
69	...	...	...	...
70	...	...	...	...
71	...	...	...	...
72	...	...	...	...
73	...	...	...	...
74	...	...	...	...
75	...	...	...	...
76	...	...	...	...
77	...	...	...	...
78	...	...	...	...
79	...	...	...	...
80	...	...	...	...
81	...	...	...	...
82	...	...	...	...
83	...	...	...	...
84	...	...	...	...
85	...	...	...	...
86	...	...	...	...
87	...	...	...	...
88	...	...	...	...
89	...	...	...	...
90	...	...	...	...
91	...	...	...	...
92	...	...	...	...
93	...	...	...	...
94	...	...	...	...
95	...	...	...	...
96	...	...	...	...
97	...	...	...	...
98	...	...	...	...
99	...	...	...	...
100	...	...	...	...

HD20-10PMFS-SN8001

DWG NO	
--------	--

HD20-10PMFS-SN8001

CUSTOMER	
----------	--

CUSTOMER	ALTW
----------	------

DESIGNED BY	DATE
DRAWN BY	DATE

Vicky

CHECKED BY	
------------	--

1

	APPROVED BY
--	-------------

APPROVED BY
Lisa

	DATE
--	------

2016-05-03

	DATE
--	------

2016-05-03

	DATE
--	------

DATE	2016-05-03
------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HD20-10PMFS-SN8001](#)