



P.C.B LAYOUT
TOP VIEW



POLE		2	3	4	5	6	7	8	9	10	11	12
Dim L		10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
Dim P		5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00
Tol.	±0.15						±0.20					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
Dim L	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00	120.00
Dim P	60.00	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00
Tol.	±0.30						±0.40					

SIGN	DATE	DESCRIPTION	APPROVER
△	01/12'07	Part No. is changed	Tason
△	01/12'07	Soldering temperature changed from 245° to 250°	Tason
△	2/12'09	Operating temperature changed (-40°C to +115°C)	Tony
△	2/12'09	Add "VDE" Safety Approval	Tony
△	8/19'13	update the drawing	Guoxue
△	8/19'13	Current rating is changed from 10A to 16A.	Guoxue
△	8/19'13	Soldering temperature is changed from 250°C ±10°C/5 Sec to 260°C ±5°C/5 Sec	Guoxue
△	8/19'13	Part No is changed	Guoxue
△	5/23'16	Part No is changed	Guoxue

Material: ● Item ① Terminal housing : Thermoplastic (UL94V-0)

● Item ② Clamp : Brass, Ni plated

● Item ③ Wire guard solder pin : Brass, Tin plated.

● Item ④ Terminal screw: Steel Zinc plating "-" slot type

Electrical:	cULus	VDE	CQC
● Voltage rating:	300V	250V	250V
● Current rating:	16A	10A	24A
● Wire range:	0.34-4.0 mm ²		0.2-2.5 mm ²
● Solid wire(AWG):	12-22		
● Stranded wire(AWG):	12-22		
● Toque:	3.5Lb-In	0.4 Nm	0.4 Nm
● Screw:	M2.5		
● Wire strip length:	6-7mm		
● Withstanding Voltage:	1.6KV	2KV	2.5KV
● Operating temperature:	-40°C to +115°C		
△ △ ● Soldering temperature:	260°C ±5°C/5 Sec		

△ △ ● Safety Approval:



△ ● Critical dimension:

△ △ TI xx 01 x 0 xxxx G

02 2 POLES
03 3 POLES
...
24 24 POLES

COLOR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

0000:"@ "Logo (Standard)
000A:"ANYTEK"Logo
0091:"ANYTEK"Logo
Any special item by
customer request,
please contact sales department.

G RoHS compliant
(lead<4%)
In copper Alloy

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TI-5.0 series (配YD-5.0脚子)						
PART NO.	TIxx01x0xxxxG			DWG NO.	8TI0003		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Chen Bo 05/23'16	Guoxue 2013.09.24				UNIT: mm SCALE: NONE
				SHEET: 01/01		REV.: G	



SHEET: 01/01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>TI0201800000G</u>	<u>TI0301800000G</u>	<u>TI0401800000G</u>	<u>TI0801800000G</u>	<u>TI0201500000G</u>	<u>TI0301500000G</u>
<u>TI0401500000G</u>	<u>TI0501500000G</u>	<u>TI0601500000G</u>	<u>TI0701500000G</u>	<u>TI0801500000G</u>	<u>TI0901500000G</u>
<u>TI1001500000G</u>	<u>TI1101500000G</u>	<u>TI1201500000G</u>	<u>TI1301500000G</u>	<u>TI1401500000G</u>	<u>TI1501500000G</u>
<u>TI1601500000G</u>	<u>TI1701500000G</u>	<u>TI1801500000G</u>	<u>TI1901500000G</u>	<u>TI2001500000G</u>	<u>TI2101500000G</u>
<u>TI2201500000G</u>	<u>TI2301500000G</u>	<u>TI2401500000G</u>			