




SIGN	DATE	DESCRIPTION	APPROVER
△	2010.03.31	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal(up body): Thermoplastic (UL94V-0)
- Item ② Terminal(down body): Thermoplastic (UL94V-0)
- Item ③ Female contact: PhBz ,Tin plated
- Item ④ Clamp: Brass(CuZn) Ni plated
- Item ⑤ Terminal screw: Steel Zinc plating "--" slot type

Electrical: cULus

- Voltage rating:300 V
- Current rating:20 A
- Wire range:
- Solid wire(AWG):12-22
- Stranded wire(AWG):12-22
- Torque:4 Lb-In
- Screw:M3
- Wire strip length:7-8 mm
- Withstanding Voltage: 1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval: cULus



EM xx 7 1 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
24: 24 POLES

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G: Pb<40000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

POLE		2	3	4	5	6	7	8	9	10	11	12
A		10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
B		5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00
Tol.	±0.15						±0.20					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00	120.00
B	60.00	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00
Tol.	±0.25						±0.30					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	EM-5.0 W/O Flange Series										
PART NO.	EMxx71x0xxxxG				DWG NO.	8EM0202					
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.						Tolerance	
		Jacke 2010.04.01	Jacke 2010.04.01				UNIT: mm		X.	±0.50	
							SCALE: NONE		X.X	±0.30	
									X.XX	±0.10	
				SHEET: 01/01			REV: C		X°	±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>EM0271500000G</u>	<u>EM0371500000G</u>	<u>EM0471500000G</u>	<u>EM0671500000G</u>	<u>EM0771500000G</u>	<u>EM0871500000G</u>
<u>EM0971500000G</u>	<u>EM1071500000G</u>	<u>EM1171500000G</u>	<u>EM1271500000G</u>	<u>EM1371500000G</u>	<u>EM1471500000G</u>
<u>EM1571500000G</u>	<u>EM1671500000G</u>	<u>EM1771500000G</u>	<u>EM1871500000G</u>	<u>EM1971500000G</u>	<u>EM2071500000G</u>
<u>EM2171500000G</u>	<u>EM2271500000G</u>	<u>EM2371500000G</u>	<u>EM2471500000G</u>	<u>EM0271800000G</u>	<u>EM0271400000G</u>
<u>EM0471400000G</u>					