




PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
A	DCN 41768	10/15	BNK



MATERIAL:

- BODIES:

CONTACT:

CRIMP RING:

INSULATOR:

O-RING:

LOCKWASHER:
- STAINLESS STEEL PER AMS-5640,
ALLOY UNS S30300, TYPE 1

BERYLLIUM COPPER PER ASTM B196,
ALLOY No. UNS C17300, TD04

BRASS PER ASTM B16, ALLOY UNS No. C36000

PTFE PER ASTM D1710, TYPE I, GRADE 1, CLASS B

SILICONE RUBBER PER A-A-59588,
CLASS 2B, GRADE 50/60

300 SERIES STAINLESS

FINISH:

- BODY:

CONTACT:
- PASSIVATED PER AMS-2700

GOLD PER ASTM B488, TYPE II,
CODE C, CLASS 1.27, OVER NICKEL
PER AMS-QQ-N-290, CLASS 1, .00005" MIN.
- CRIMP RING:
- NICKEL PER AMS-QQ-N-290, CLASS

PERFORMANCE:

- IMPEDANCE:

FREQ. RANGE:


VSWR:

INSERTION LOSS:
- 50 OHMS

DC TO 12.4 GHz

1.15 + .02(F):1 DC TO 12.4 GHz

.06 X SQRT(F(F IN GHz))



RECOMMENDED MOUNTING HOLE

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: $\pm 1/64$ ANGULAR: X° $\pm 1^{\circ}0'$
-----------	-----------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M39012/59-3026](#)