

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 37960	01/11	STW

MATERIAL:

**BODY &
BUSHING:**

CENTER PIN &
OUTER RING:

GLASS:

BERYLLIUM COPPER PER ASTM B196,
ALLOY No. UNS C17300, TD04

KOVAR PER ASTM-F15

CORNING #7070

FINISH:

**BODY &
BUSHING:**

CENTER PIN &
OUTER RING:

GOLD PER ASTM B488, TYPE II,
CODE C, CLASS 1.27, OVER NICKEL
PER AMS-QQ-N-290, CLASS 1, .00005" MIN.

GOLD PER ASTM B 488, TYPE I,
CODE C, CLASS 1.27, OVER NICKEL
PER AMS-QQ-N-290, CLASS 1, .00005" MIN.

PERFORMANCE:

IMPEDANCE:


FREQ. RANGE:

VSWR:

50 OHMS
DC TO 26.5 GHz
1.25:1 DC TO 18.0 GHz
1.35:1 DC TO 26.5 GHz

TEMP. RATING:

-65°C TO +165°C



MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1"0" X°X' ±15'		UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA. S' ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		SV Microwave, Inc. 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH:	SEE NOTES	DECIMAL: X ±.030 XX ±.010 XXX ±.005				TITLE: SMP MALE, THREADED HERMETIC SB SHROUD FEED THROUGH CONNECTOR	
SURFACE AREA:	N/A	INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994				SIZE B CAGE CODE DWG. NO. 1211-40008	
PROPRIETARY		THIRD ANGLE PROJECTION		DRAWN: FED 01/18/11		SCALE: 12:1	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.				CHECKED: STW 01/18/11		SHEET 1 OF 1	
				APPROVED: STW 01/18/11			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1211-40008](#)