

# Triaxial switchable junction boxes

## VLT series

### SPECIFICATIONS

<b>Triaxial sensor inputs</b>	6
<b>Output connector</b>	5 pin, M12
<b>Material, user-selected</b>	fiberglass or stainless steel
<b>Dimensions</b>	10 x 8 x 4 in., 1-6 channels
<b>Hinge</b>	stainless steel continuous weld
<b>Latch</b>	stainless steel butterfly knob
<b>Input fittings, user-selected</b>	cable grips or 5 socket M12 connectors
<b>Terminal block connectors</b>	screw type connectors, 5 positions per channel
<b>Rating:</b>	
<b>fiberglass</b>	NEMA 4X/IP66
<b>stainless steel</b>	NEMA 4/IP66
<b>Mounting</b>	4 stainless steel feet (fiberglass model includes configurable feet)
<b>Sensor support</b>	triaxial
<b>Channel selector</b>	6 position dial switch, differential switching

**Accessories supplied:** Transducer location log; mounting feet; grounding lug; cable grip plugs (if applicable)




### Key features

- For use with triaxial sensors
- Available with M12 connectors for use with data collectors
- Manufactured in ISO 9001 facility

### Models available

Channels	Size	Material	Input connector	Model number
6	10 x 8 x 4 in.	Fiberglass	M12	VLT6FM12
			Cable grip	VLT6FG
		Stainless steel	M12	VLT6SM12
			Cable grip	VLT6SG



Note: Due to continuous process improvement, specifications are subject to change without notice.  
This document is cleared for public release.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[VLT6FG](#) [VLT6SG](#) [VLT6SM12](#) [VLT6FM12](#)