




SIGN	DATE	DESCRIPTION	APPROVER
△	02/29'12	The real product doesn't comply with the drawing, remove this step	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Section P-P

Material:

- Item a :Terminal housing:Thermoplastic (UL94 V-0)
- Item b :With flange screw: Steel Zinc plated, M2.5"/+/-"

Electrical (Match with A0 3.81 series)

- Voltage rating: 160V
- Current rating: 8A
- Wire range: 1.0~1.2mm²
- Withstanding Voltage: 1.32KV
- Critical dimension: ▽

KI xx 30 x 2 xxxx G		RoHS compliant (lead<4%) In copper Alloy
No. of poles		
02 2 CONTACTS	0 Black (RAL9005)	0000:"@ "Logo (Standard)
03 3 CONTACTS	2 Red (RAL3001/D)	000A:"ANYTEK"Logo
...	3 Orange(RAL2011/P)	Any special item by
24 24 CONTACTS	4 Yellow(RAL1018/A)	customer request,
	5 Green(RAL6018/T)	please contact sales
	6 Blue (RAL5015/A)	department.
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

Dim.A=(N-1)x3.81+14.20				
Dim.B=(N-1)x3.81				
Dim.C=(N-1)x3.81+4.60				
Poles	2P~6P	7P~12P	13P~18P	19P~24P
Dim.A	+/-0.20	+/-0.25	+/-0.30	+/-0.35
Dim.B	+/-0.15	+/-0.20	+/-0.25	+/-0.30
Dim.C	+/-0.20	+/-0.25	+/-0.30	+/-0.35

ANYTEK				CUSTOMER COPY			
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	KI 3.81 Series 2P~24P Body (With flange & W/o high profile)						
PART NO.	Klxx30x2xxxxG			DWG NO.	8KI0003		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Aaron 2012.02.29	kind 2008.9.16		UNIT: mm	X. ±0.5	
					SCALE: NONE	X.X ±0.3	
						X.XX ±0.1	
				SHEET: 01/01	REV: C	X° ±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>KI0230520000G</u>	<u>KI0330520000G</u>	<u>KI0430520000G</u>	<u>KI0530520000G</u>	<u>KI0630520000G</u>	<u>KI0730520000G</u>
<u>KI0830520000G</u>	<u>KI0930520000G</u>	<u>KI1030520000G</u>	<u>KI1130520000G</u>	<u>KI1230520000G</u>	<u>KI1330520000G</u>
<u>KI1430520000G</u>	<u>KI1530520000G</u>	<u>KI1630520000G</u>	<u>KI1730520000G</u>	<u>KI1830520000G</u>	<u>KI1930520000G</u>
<u>KI2030520000G</u>	<u>KI2130520000G</u>	<u>KI2230520000G</u>	<u>KI2330520000G</u>	<u>KI2430520000G</u>	