



N = Number of poles

Dim A=Nx5.08+1.0

Dim B=(N-1)x5.08

Dim C=Nx5.08+2.1

	Dim A	Dim B	Dim C
2-6p	±0.10	±0.15	±0.15
7-12p	±0.20	±0.20	±0.20
13-16p	±0.30	±0.25	±0.25
17-24p	±0.40	±0.35	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△			


THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item :Terminal housing:Thermoplastic (UL94 V-0)
- Item :Hexagon nut : Brass , M2.5

Electrical (Match with AR series)

- Voltage rating: 300V
- Current rating: 10A
- Wire range: 1.5~2.5mm²
- Withstanding Voltage: 1.6KV



Section A-A

KV xx 50 x 5 xxxxx G

No. OF POLES

02 2 CONTACTS

03 3 CONTACTS

...

24 24 CONTACTS

Color

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

G: Pb<40000ppm

0000: "@" Logo (Standard)


000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KV 5.08 SERIES (Flange With Nut & High profile)						
PART NO.	KVxx50x5xxxxG			DWG NO.	8KV0006		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Kind	Kind			Tolerance	
		2009.12.15	2009.08.10			UNIT: mm	X. ±0.50
				SHEET: 01/01		SCALE: 2/1	X.X ±0.30
						REV.: B	X.XX ±0.10
							X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>KV0250550000G</u>	<u>KV0350550000G</u>	<u>KV0450550000G</u>	<u>KV0550550000G</u>	<u>KV0650550000G</u>	<u>KV0750550000G</u>
<u>KV0850550000G</u>	<u>KV0950550000G</u>	<u>KV1050550000G</u>	<u>KV1150550000G</u>	<u>KV1250550000G</u>	<u>KV1350550000G</u>
<u>KV1450550000G</u>	<u>KV1550550000G</u>	<u>KV1650550000G</u>	<u>KV1750550000G</u>	<u>KV1850550000G</u>	<u>KV1950550000G</u>
<u>KV2050550000G</u>	<u>KV2150550000G</u>	<u>KV2250550000G</u>	<u>KV2350550000G</u>	<u>KV2450550000G</u>	