




REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASE NEW DWG FORMAT	Jun.16.2014	Tod	Tommy
B2	-	UPDATE THE PART NUMBER	Jun.27.2015	Drack	Tommy



- NOTES: UNLESS OTHERWISE SPECIFIED
- MATERIAL:
BODY: ZINC DIE CAST, NICKEL PLATED
BOOT: TPE(BLACK)
 - SPECIFICATIONS:
2.1 DEGREE OF PROTECTION: IP67 (MATED CONDITION)
MUST BE POTTED TO ACHIEVE IP67 RATING
2.2 RoHS COMPLIANT
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



	Cable OD Range
1	MA4FSR-A8.5 7.5~8.5 mm
2	MA4FSR-A10.5 9.5~10.5 mm
3	MA4FSR-A12.8 11.5~12.8 mm



QUANTITY	SEE PART NUMBER CHART	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST				
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in millimeters. 2) Tolerances are as follows: 1 R1, DEC ±0.30 Fractions ±1/64 2 R1, DEC ±0.30 Angles ±1° 3 R1, DEC ±0.08 3) Note reference =				
MATERIAL SPECIFICATIONS:				
PROCESS SPECIFICATIONS:				
NEXT ASSY:				
SIGNATURES				
DATE				
CHECKED				
ENGINEER				
APPROVAL				
CUSTOMER				
M23A, Flexible Strain Relief				
Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036				
SIZE				
TYPE				
DWG NO:				
MA4FSR-Axxx				
REVISION				
B2				
SCALE				
NONE				
SHEET 1 OF 1				

TITLE:

M23A,Flexible Strain Relief

DWG NO:

MA4FSR-Axxx

REV: B2

SH: 1

OF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MA4FSR-A10.5](#)