

[illegible]

1		2		3		4		5		6	
PRODUCT NUMBER	NO OF POS	MATING LENGTH DIM H	OVERALL LENGTH DIM K	DIM L	TAIL LENGTH DIM "M"						
78207-X06	2 X 3	.230/5.84	.300/7.62	.200/5.08	.120/3.05						
-X08	2 X 4	.230/5.84	.400/10.16	.300/7.62							
-X10	2 X 5	.230/5.84	.500/12.70	.400/10.16							
-X12	2 X 6	.230/5.84	.600/15.24	.500/12.70							
-X14	2 X 7	.230/5.84	.700/17.78	.600/15.24							
-X16	2 X 8	.230/5.84	.800/20.32	.700/17.78							
-X18	2 X 9	.230/5.84	.900/22.86	.800/20.32							
-X18A	2 X 9	.210/5.33	.900/22.86	.800/20.32		NOTE 7					
-X20	2 X 10	.230/5.84	1.000/25.40	.900/22.86							
-X22	2 X 11	.230/5.84	1.100/27.94	1.000/25.40							
-X24	2 X 12	.230/5.84	1.200/30.48	1.100/27.94							
-X26	2 X 13	.230/5.84	1.300/33.02	1.200/30.48							
-X28	2 X 14	.230/5.84	1.400/35.56	1.300/33.02							
78207-X30	2 X 15	.230/5.84	1.500/38.10	1.400/35.56	.120/3.05						
78207-X32 THRU 78207-X72	UNAVAILABLE										
78207-X80	2 X 4	.230/5.84	.400/10.16	.300/7.62	.100/2.54						

NOTES:

1. MOLDING MAT'L: GLASS REINFORCED PCT, COLOR: BLACK
FLAME RETARDANT PER UL 94 V-0
MAXIMUM OPERATING TEMPERATURE: 130° C.

2. PIN MATERIAL: 3/4 HD PHOS. BRZ.

③ NO SLOTS ON 2 X 5 POSITION OR SMALLER PRODUCT. THE CENTER KEY SLOT WILL BE ON ALL HEADERS REGARDLESS OF SIZE.

④ TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED, BOTH ENDS.

⑤ COMPANY LOGO MAY APPEAR IN THIS AREA.

⑥ "T" ATTACHED TO THE P/N INDICATES PARTS ARE TO BE PACKAGED IN TUBES.

⑦ CUSTOMER SPECIAL -- "A" SUFFIX INDICATES 0.210/5.33 MATING LENGTH.

⑧ ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION, NOT AVAILABLE FOR -5YY, -5YYH, -6YY & -6YYH.

⑨ PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.

⑩ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

⑪ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

⑫ "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."

PIN PLATING CODES									
-1YY	30u"/.76u (SEE NOTE 11) 50u"/1.27u Ni								
-2YY	15u/.38u (SEE NOTE 11) 50u"/1.27u Ni								
-3YY	50u"/1.27u Au 50u"/1.27u Ni								
-4YY	100u"/2.54u MIN Sn 50u"/1.27u Ni (SEE NOTE 12)								
-4YYHLF									
-5YY	15u"/.38u (SEE NOTE 11) 50u"/1.27u Ni								
-6YY	30u"/.76u (SEE NOTE 11) 50u"/1.27u Ni								
-7YY	30u"/.76u Au OVER 50u"/1.27u Ni								
-8YY	15u"/.38u Au OVER 50u"/1.27u Ni								

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection		product family HEADER	
ltr	ecn no	dr	date	tolerances unless otherwise specified				INCH/MM scale 3:1		title	
R				angles	linear	XX±.01/XX±.03 .XXX±.005/XX±0.13 .000X±.0020/XXX±0.05	FRICION LATCH HEADER DOUBLE ROW, R/A				
				dr	S.ROYER	01/21/94	FCJ		dwg no		sheet 2 of 2 size
				enrg	L.FYE	01/21/94			78207		A3
				chr	L.FYE	01/21/94			type		Product Customer Drawing
				appd	L.FYE	01/21/94					
sheet index	revision sheet										

FCJ
FCconnect.com
Copyright FCJ

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[78207-112THLF](#)