





PRODUCT NO.  
61729



## TYPE"1" FULL BACK



## TYPE"2" PARTIAL BACK

- NOTES:
1. MATERIAL:  
SHIELD & CONTACTS: COPPER ALLOY  
HOUSING: UL 94V-0 THERMOPLASTIC. COLOR: SEE PRODUCT NUMBER CODE.
  2. PLATING: SEE PRODUCT NUMBER CODE.  
SHIELD: BRIGHT TIN  
NICKEL UNDERPLATE.
  3. DATUMS & BASIC DIMENSIONS TO BE DETERMINED BY CUSTOMER
  4. RECOMMENDED BOARD THICKNESS IS 1.57 mm (.062)
  5. PACKING STANDARD GS-14-920 WILL BE APPLIED FOR LEAD FREE P/N'S
  6. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008
  7. FOR LEAD FREE P/N'S, THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 40 SECONDS IN A CONNECTION, INFRO-RED OR VAPOR PHASE REFLOW OVEN.

mat'l. code			tolerances unless otherwise specified			CUSTOMER		title		product family		code	
ltr	pcn no	dr	date	linear		COPY	projection	FCI	Electronics	USB	RECEPTACLE B TYPE	sheet	2 of 2
P				.00 ± 0.10	.000 ± 0.05					61729			
				angles ± 2°									
				dr	SHIRLEY HSU 03/03/97								
				engr	R Y LUU 03/03/97								
				chr	R Y LUU 03/03/97								
				dppld	JENN TSAO 03/03/97								
sheet	revision												
index	sheet												

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[61729-1011BLF](#)