

61082-AA B C D E FF

AA	POSITION
04	2X20
06	2X30
08	2X40
10	2X50
12	2X60
14	2X70
16	2X80
18	2X90
20	2X100

B	FOR PLUG, SEE DWG. NO. 61083			
COMBINATION OF MATED HEIGHT	Plug 1	Plug 2	Plug 3	Plug 4
Recep 1				
Recep 2				
Recep 3				

E	PACKAGING
0	TUBE WITHOUT METAL CAP
2	T&R WITH METAL CAP
9	TUBE WITH METAL CAP
6	T&R WITHOUT METAL CAP (WITH KAPTON TAPE)

D	POLARIZATION PEG	HOLD DOWN
0	YES	NO
2	NO	NO


C	PLATING ON CONTACT AREA	FF
0	GOLD 0.2um MIN / TIN LEAD NICKEL UNDERPLATE OVERALL 1.27um MIN	NONE
1	GOLD FLASH (0.1um MIN) OVER PALLADIUM-NICKEL 0.76um MIN / TIN LEAD NICKEL UNDERPLATE OVERALL 1.27um MIN	NONE
4	GOLD 0.2um MIN / PURE TIN 2um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF
5	GOLD 0.38um MIN / PURE TIN 2um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF
6	GOLD FLASH (0.1um MIN) OVER PALLADIUM-NICKEL 0.76um MIN / PURE TIN 2um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF

- NOTES:
- MATERIAL
HOUSING: LCP UL 94V-0
TERMINAL: BERYLLIUM COPPER
 - PLATING
AS SHOWN IN TABLE.
 - SEE GS-12-547 FOR PRODUCT SPEC.
 - SEE GS-15-551 AND GS-14-816 FOR THE DETAILS OF PACKAGING.
PRODUCT WILL BE PACKED IN ACCORDANCE TO GLOBAL PROCEDURE GS-14-920.
 - PACKAGING OPTION 2: "NOT ALL SIZES AVAILABLE; CHECK WITH FACTORY".
 - THIS PRODUCT MEETS THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - THE HOUSING WITH WITHSTAND EXPOSURE UP TO 260° PEAK TEMPERATURE FOR 30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR REFLOW OVEN.
 - PLATING OPTION "4" IS LEADFREE ALTERNATIVE FOR OPTION "0", AND OPTION "6" IS LEADFREE ALTERNATIVE FOR OPTION "1".
 - HIGH PRECISION COPLANARITY IS AVAILABLE FOR 2X80 TO 2X100 POS, ALL HEIGHTS. PLS REFER TO PRINT 10069524.
 - A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

rev	ecn no	dr	date
W	S07-0166	MCH	2007-05-16
X	S07-0416	MCH	2007-11-22
Y	S08-0330	MCH	2008-10-08
AA	S09-0311	MCH	2009-10-06
T	S04-0133	MW	2004-06-23
U	S04-0167	CH	2004-07-30
V	S04-0098	CH	2005-03-31

www.fciconnect.com			surface ISO 1302		- 	tolerance std ISO 406 ISO 1101		projection 	MM 				
			TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	M. Cheong	2009-06-01	ANGULAR	LINEAR		0.X	±0.20	size A3	Scale 17:1				
Eng	M. Cheong	2009-06-01				0.XX	±0.15						
Chr	M. Cheong	2009-06-01				0.XXX	±0.10						
Appr	Joey Ng	2009-10-06	0°	±2°				ECN	S09-0311				
Product family		BERGSTAK							Spec ref				
		title				BERGSTAK 0.8MM				dwg no	61082		Rev. AA
		RECEPTACLE ASSY											
		catalog no				-							
		CUSTOMER				sheet 1 of 6							



PRODUCT NO.	NUMBER OF POSITIONS	DIMENSION		
		A	B	C
61082-041***	2X20	15.2	21.8	20.2
61082-061***	2X30	23.2	29.8	28.2
61082-081***	2X40	31.2	37.8	36.2
61082-101***	2X50	39.2	45.8	44.2
61082-121***	2X60	47.2	53.8	52.2
61082-141***	2X70	55.2	61.8	60.2
61082-161***	2X80	63.2	69.8	68.2
61082-181***	2X90	71.2	77.8	76.2
61082-201***	2X100	79.2	85.8	84.2



COPLANARITY OF TAIL:
0.1 MAX. APPLIED TO 2X20 TO 2X70 POS.
0.13 MAX APPLIED TO 2X80 TO 2X100 POS.

HIGH PRECISION COPLANARITY IS AVAILABLE
FOR 2X80 TO 2X100 POS.
PLS REFER TO PRINT 10069524.

DETAIL A
SCALE 10:1




RECEPTACLE 1




title BERGSTAK 0.8MM
RECEPTACLE ASSY
catalog no -

dwg no 61082
Rev. AA
CUSTOMER sheet 2 of 6


RECEPTACLE I



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X20, 2X30, 2X40, 2X50, 2X60




RECOMMENDED PCB LAYOUT WITHOUT PEGS AND HOLDDOWN



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X70, 2X80, 2X90, 2X100

FCI	title	BERGSTAK 0.8MM	dwg no	61082	Rev.
		RECEPTACLE ASSY			AA
	catalog no	-	CUSTOMER	sheet 3 of 6	

PRODUCT NO.	NUMBER OF POSITIONS	DIMENSION		
		A	B	C
61082-042***	2X20	15.2	21.8	20.2
61082-062***	2X30	23.2	29.8	28.2
61082-082***	2X40	31.2	37.8	36.2
61082-102***	2X50	39.2	45.8	44.2
61082-122***	2X60	47.2	53.8	52.2
61082-142***	2X70	55.2	61.8	60.2
61082-162***	2X80	63.2	69.8	68.2
61082-182***	2X90	71.2	77.8	76.2
61082-202***	2X100	79.2	85.8	84.2




AA

COPLANARITY OF TAIL
0.1 MAX APPLIED TO 2X20 TO 2X70 POS.
0.13 MAX APPLIED TO 2X80 TO 2X100 POS.

HIGH PRECISION COPLANARITY IS AVAILABLE
FOR 2X80 TO 2X100 POS.
PLS REFER TO PRINT 10069524.

DETAIL C
SCALE 8:1



RECEPTACLE 2



title BERGSTAK 0.8MM
RECEPTACLE ASSY
catalog no -

dwg no




61082

Rev.
AA

CUSTOMER

sheet 4 of 6


PRODUCT NO.	NUMBER OF POSITIONS	DIMENSION		
		A	B	C
61082-043***	2X20	15.2	21.8	20.2
61082-063***	2X30	23.2	29.8	28.2
61082-083***	2X40	31.2	37.8	36.2
61082-103***	2X50	39.2	45.8	44.2
61082-123***	2X60	47.2	53.8	52.2
61082-143***	2X70	55.2	61.8	60.2
61082-163***	2X80	63.2	69.8	68.2
61082-183***	2X90	71.2	77.8	76.2
61082-203***	2X100	79.2	85.8	84.2



COPLANARITY OF TAIL
0.1 MAX APPLIED TO 2X20 TO 2X70 POS
0.13 MAX APPLIED TO 2X80 TO 2X100 POS.

HIGH PRECISION COPLANARITY IS AVAILABLE
FOR 2X80 TO 2X100 POS.
PLS REFER TO PRINT 10069524.

DETAIL E
SCALE 8:1



RECEPTACLE 3



title BERGSTAK 0.8MM
RECEPTACLE ASSY
catalog no -


dwg no 61082

Rev.
AA


CUSTOMER

sheet 5 of 6


RECEPTACLE 2 & 3



RECOMMENDED PCB LAYOUT WITHOUT PEGS AND HOLDDOWN



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X20, 2X30, 2X40, 2X50, 2X60



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X70, 2X80, 2X90, 2X100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

[61082-042622LF](#) [61082-061622LF](#) [61082-061629LF](#) [61082-083622LF](#) [61082-102622LF](#) [61082-103622LF](#) [61082-123622LF](#) [61082-141622LF](#) [61082-141629LF](#) [61082-142622LF](#) [61082-163429LF](#) [61082-183622LF](#) [61082-183629LF](#) [61082-201629LF](#) [61082-041522LF](#) [61082-043429LF](#) [61082-043622LF](#) [61082-062429LF](#) [61082-063509LF](#) [61082-063622LF](#) [61082-081622LF](#) [61082-103502LF](#) [61082-123502LF](#) [61082-141429LF](#) [61082-142429LF](#) [61082-142629LF](#) [61082-143522LF](#) [61082-143622LF](#) [61082-163522LF](#) [61082-163622LF](#) [61082-041502LF](#) [61082-042502LF](#) [61082-043022](#) [61082-141502LF](#) [61082-162509LF](#) [61082-121622LF](#) [61082-081422LF](#) [61082-103422LF](#) [61082-201422LF](#) [61082-181422LF](#) [61082-101422LF](#) [61082-061422LF](#) [61082-141422LF](#) [61082-161422LF](#) [61082-123422LF](#) [61082-102422LF](#) [61082-202422LF](#) [61082-203422LF](#) [61082-183422LF](#) [61082-083422LF](#) [61082-142422LF](#) [61082-163422LF](#) [61082-121422LF](#) [61082-041422LF](#) [61082-182422LF](#) [61082-082422LF](#) [61082-162422LF](#) [61082-043422LF](#) [61082-122422LF](#) [61082-082502LF](#) [61082-082622LF](#) [61082-121529LF](#) [61082-122502LF](#) [61082-043502LF](#) [61082-083429LF](#) [61082-063522LF](#) [61082-041622LF](#) [61082-201502LF](#) [61082-202509LF](#) [61082-161509LF](#) [61082-201509LF](#) [61082-082522LF](#) [61082-083522LF](#) [61082-103522LF](#) [61082-101622LF](#) [61082-122622LF](#) [61082-102502LF](#) [61082-182502LF](#) [61082-041429LF](#) [61082-082509LF](#) [61082-101522LF](#) [61082-081429LF](#) [61082-101502LF](#) [61082-181502LF](#) [61082-183502LF](#) [61082-062502LF](#) [61082-062522LF](#) [61082-161502LF](#) [61082-163502LF](#) [61082-041509LF](#) [61082-162429LF](#) [61082-143502LF](#)