



DIMENSIONS



TERMINATION



TIN LEAD PART NUMBER

PART NUMBER


86093967113755957E1

LEAD FREE PART NUMBER

PART NUMBER

86093967113755DHLF

P.C. CARD DRILLING (Component side view)



SPECIFICATION 957 or SPECIFICATION DH= 17 grounding pins h= 5.4mm in position
 row : a cavity : 2-7-15-23-32
 row : b cavity : 1-8-15-17-24-32
 row : c cavity : 1-8-14-20-31-32
 1 grounding pins h= 4.2mm in position
 row : c cavity : 24

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
 SEE DRAWING C-8609-0000A

European Views

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	LE GALLIC	2005/11/23	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1.5		
Eng	H. LEGALLIC	2005/11/23			0.XX	±0.1		ECN LS06-0097		
Chr	LEGARE	2005/11/23			0.XX' ±2"	±0.1				
Appr	LEGARE	2005/11/23	Product family DIN 8609				Spec ref -			
			title STANDARD MALE RA 3 ROW 96 CONTACTS				dwg no C-8609-1207		Rev	
									B	
			catalog no		-		CUSTOMER		sheet 1 of 1	

rev	ecn no	dr	date
A	LS05-0070	-	2005/11/23
B	LS06-0097	LGO	2006/07/26
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

REV F - 2006-04-17

Copyright FCI.

PDM: Rev:B

STATUS: Released

Printed: May 14, 2011

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86093967113755DHLF](#)