





REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASE NEW DWG FORMAT	Sep-30-2019	Flan	Tommy



- NOTES: (UNLESS OTHERWISE SPECIFIED)
- MATERIAL: COPPER ALLOY, SILVER PLATED
 - SPECIFICATIONS:
 - 2.1 RATED CURRENT: 45 A(MAX)
 - 2.2TERMINATION TYPE: CRIMPING
 - 2.3 AVAILABLE WIRE RANGE: 2(8AWG) TO 10MM
 - 2.4 RoHS COMPLIANT
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



SECTION A-A



		SEE PART NUMBER CHART					
QUANTITY	PART NUMBER		DESCRIPTION			REV	
MATERIALS LIST							
<div>UNLESS OTHERWISE SPECIFIED: 1) All Dimensions are in mm.(mm) 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.00 3) Hole reference = </div>		<div>SIGNATURES</div> <div>DATE</div> <div>DRAWN: Flm Sep-30-2019</div> <div>CHECKED: Kadin Sep-30-2019</div> <div>ENGINEER:</div> <div>APPROVAL: Tommy Sep-30-2019</div> <div>CUSTOMER:</div>		<div>Amphenol</div> <div>Sine Systems – www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036</div>			
MATERIAL SPECIFICATIONS:				PIN CONTACT WITH RADSOK TECHNOLOGY. CRIMP BARREL, SIZE 8(3.6MM) WIRE RANGE 10MM, 8AWG			
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		SIZE	TYPE	DWG NO:	REV
NEXT ASS'Y:				B	C	MP&ARS3S-10	B1
				SCALE: 2 : 1		SHEET 11 OF	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MP6ARS8S-10](#)