







- NOTES:
- 1-Material: Phosphor bronze,thickness 0.20
 - 2-Finish on contact area:see table
finish on termination:bright tin over nickel
 - 3-Wire range:20-24 AWG(see ref sheet 1/2)
 - 4-Max outer dia of wire insulator:
-1.73 mm for contact #20-24
-1.02 mm for contact #24-28
 - 5-Current carrying capacity per contact:
5.Amps max when crimped to #20 AWG
5 Amps max when crimped to #22 AWG
3 Amps max when crimped to #24 AWG
2 Amps max when crimped to #26 AWG
1 Amps max when crimped to #28 AWG
 - 6-After 5 insertions into connector,
contact retention must be 5 pounds axial load min
 - 7-When contact is crimped to 20 AWG,the insulation
support crimped height must be 1.78 mm max to ensure
a proper insertion into housing
 - 6-Packaging:box of 500 contacts

NOTE : ROHS INFORMATION
The LF products meet European union directives and other
country regulations as described in GS-22-008
Terminations plating spec : 2um Nickel min + 2um Sn min
Packaging Spec : see GS-14-920

PART NUMBER	Plating
8656453067LF	0.4μ Au / GXT
8656453067	0.4μ Au / GXT

www.fciconnect.com		surface - ☒ ISO 1302	tolerance std ISO 406 ISO 1101	projection	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	-	2003-04-18	ANGULAR	0.X ±0.3	size A3
Eng	ABHILASH M R	2009-07-07	LINEAR	0.XX ±0.1	Scale 10/1
Chr	ABHILASH M R	2009-07-07	0° ±2°	0.XXX ±0.05	ECN 111-0003
Appr	SUDHIR VARMA	2009-07-07	Product family	8656	Spec ref -
		FCi CRIMP CONTACTS		dwg no C01-8656-0420	Rev. K
		catalog no -		sheet 1 of 1	

rev	ecn no	dr	date
K	111-0003	AMR	2011-01-06
-	-	-	-
E	LS08-0167	MPE	2008/08/05
F	LS08-0216	MPE	2008/11/26
G	109-0128	AMR	2009-07-07
H	109-0152	AMR	2009-07-27
J	110-0070	AMR	2010-03-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8656453067LF](#)