

NOTES:

- 1-Material:phosphor bronze,thickness 0.20
2-Finish on contact area:see table
finish on termination:bright tin over nickel
3-Wire range:20 to 24 AWG
4-Max outer dia of wire insulator:1.73 mm
5-Current carrying capacity per contact:
5.Amps max when crimped to #20 AWG
5 Amps max when crimped to #22 AWG
3 Amps max when crimped to #24 AWG
6-After 5 insertions into connector,
contact retention must be 5 pounds axial load min
7-When contact is crimped to 20 AWG,the insulation
support crimped height must be 1.78 mm max to ensure
a proper insertion into housing
6-Packaging:Box of 500 contacts

NOTE : ROHS INFORMATIONS

The LF products meet European union directives and other
country regulations as described in GS-22-008
Terminations plating spec : 2um Nickel min + 2um Sn min
Packaging Spec : see GS-14-920

CORE RANGE

8656353067LF

0.4μ Au / GXT

8656353067

0.4μ Au / GXT

8656353065

0.76μ Au / GXT

8656353065LF

0.76μ Au / GXT

PART NUMBER

Plating

www.fciconnect.com

surface
ISO 1302

tolerance std
ISO 406 ISO 1101

projection
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED

Dr C JARRY

28/01/97

ANGULAR

LINEAR

0.X

±0.3

size

A3

Scale

10/1

Eng

Chr

Appr

0° ±2°

0.XX

±0.1

0.XXX

±0.05

ECN

III-0003

Product family

8656

Spec ref



CRIMP SOCKET

#WIRE 20-24 in box 500 cts

catalog no

dwg no

C01-8656-1530

Rev.

H

CUSTOMER

sheet 1 of 1

rev	ecn no	dr	date
C	LS06-196	MPE	27/11/2006
D	LS06-0210	MPE	2006/12/07
E	LS08-0127	MPE	2008/05/13
F	I09-0152	AMR	2009-07-27
G	I10-0070	AMR	2010-03-09
H	III-0003	AMR	2011-01-06
-	-	-	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[8656353065LF](#) [8656353067LF](#)