



mat'l. code		surface 58		tolerance		projection		product family		58SF		CODE	
ltr	ecm no	dr	date	ISO 1302	ISO 406	ISO 1101	ISO 1101	product family	58SF	JP			
A	J09-0202	M.Y	2009-5-25	tolerances unless specified		linear		SFW_S Documents Configuration (1mm Spacing connector)					
angles		linear		scale		mm		dwg no		sheet 1 of 1		size	
								JSA97525		A4			
dr		engr		chr		appd		type		Product Customer Drawing		Rev.	
												A	
sheet index		revision		A		1							

Configuration of Documents

P/N	Documents	No.	Title	CAT.No.
SFW_S-2ST(M)E9LF	Specification Connector dwg.	SC-SFWS03 JSA96516 JSA96517 JSA96518 JSA97526 JSA97527 JSA93340 JSA93341	CAT.NO.TABLE FOR 1mm SPACING SMT CONNECTOR 1mm SPACING SURFACE MOUNT FPC/FFC CONNECTOR 1mm SPACING SURFACE MOUNT FPC/FFC CONNECTOR CAT. NO. TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONN. PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR RECOMMENDED CABLE RECOMMENDED CABLE	SFW__S-2ST__LF SFW__S-2ST__LF SFW__S-2STM__LF SFW__S-2ST_E9LF SFW__S-2ST_E9LF SFW__S-2ST__LF SFW__S-2ST__LF
SFW_S-6ST(M)E9LF	Cable dwg. Manual Specification Connector dwg.	BJM-SFWS101 SC-SFWS04 JSA96521 JSA96522 JSA96523 JSA97528 JSA97529 JSA93904 BJM-SFWS102	CAT. NO. TABLE FOR 1mm SPACING SMT CONNECTOR 1mm SPACING SURFACE MOUNT CIC CONNECTOR 1mm SPACING SURFACE MOUNT CIC CONNECTOR CAT. NO. TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONN. PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR RECOMMENDED CABLE	SFW__S-6ST__LF SFW__S-6ST__LF SFW__S-6STM__LF SFW__S-6ST_E9LF SFW__S-6ST_E9LF SFW__S-6ST__LF
	Cable dwg. Manual			

CAT. NO. & DIMENSIONS

NOTE3	NO. OF CONTACTS (n)	CAT. NO.	DIMENSIONS (NOTE2)		
			A ±0.2	B ±0.2	C ±0.2
	4	SFW4S-2ST__LF	10.4	5.24	3
	5	SFW5S-2ST__LF	11.4	6.24	4
	6	SFW6S-2ST__LF	12.4	7.24	5
*	7	SFW7S-2ST__LF	13.4	8.24	6
	8	SFW8S-2ST__LF	14.4	9.24	7
*	9	SFW9S-2ST__LF	15.4	10.24	8
	10	SFW10S-2ST__LF	16.4	11.24	9
	11	SFW11S-2ST__LF	17.4	12.24	10
*	12	SFW12S-2ST__LF	18.4	13.24	11
	13	SFW13S-2ST__LF	19.4	14.24	12
	14	SFW14S-2ST__LF	20.4	15.24	13
	15	SFW15S-2ST__LF	21.4	16.24	14
	16	SFW16S-2ST__LF	22.4	17.24	15
	17	SFW17S-2ST__LF	23.4	18.24	16
*	18	SFW18S-2ST__LF	24.4	19.24	17
*	19	SFW19S-2ST__LF	25.4	20.24	18
	20	SFW20S-2ST__LF	26.4	21.24	19
*	21	SFW21S-2ST__LF	27.4	22.24	20
	22	SFW22S-2ST__LF	28.4	23.24	21
	23	SFW23S-2ST__LF	29.4	24.24	22
	24	SFW24S-2ST__LF	30.4	25.24	23
*	25	SFW25S-2ST__LF	31.4	26.24	24
	26	SFW26S-2ST__LF	32.4	27.24	25
*	27	SFW27S-2ST__LF	33.4	28.24	26
	28	SFW28S-2ST__LF	34.4	29.24	27
	29	SFW29S-2ST__LF	35.4	30.24	28
	30	SFW30S-2ST__LF	36.4	31.24	29
*	31	SFW31S-2ST__LF	37.4	32.24	30
*	32	SFW32S-2ST__LF	38.4	33.24	31

CAT. NO. SFW (n) S - 2 ST - - - LF

SERIES

NO. OF CONTACTS

STRAIGHT TYPE

FOR FPC / FFC

VARIATION

STM : FOR AUTOMATIC MOUNTING (SMT)
WITH MOUNTING PLATE

ST : FOR AUTOMATIC MOUNTING (SMT)
WITHOUT MOUNTING PLATE

PACKAGE STYLE


LEAD FREE

NOTES

- THIS PRODUCT IS THE CONNECTOR, DESIGNED TO TERMINATE FPC/FFC AND COPER WITH AUTOMATIC MOUNTING (SMT).
- SEE PART DRAWINGS FOR DIMENSIONS A.B.C.
- PLEASE CONSULT US IN CASE OF USING PARTS WITH * MARK

mat'l. code				surface 58 / tolerance ISO 1302 ✓ ISO 406 ISO 1101		projection		product family 58SF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title CAT. NO. TABLE FOR 1mm SPACING SMT CONNECTOR (CAT.No.SFW__S-2ST__LF)			
A	J05-0377	H.T	2005-6-22	angles	linear						
B	J05-0547	H.T	2005-8-30			scale X		dwg no sheet 1 of 1 size JSA 96516 A4			
C	J06-0430	H.T	2006-10-19								
D	J07-0407	H.T	2007-8-9	dr	engr	FCI		type Product Customer Drawing			
				chr	appd						
sheet index	revision	D	1								Rev. D

SC-SFWS 03 JSA96517 96518 96519 96520 93340 93341
form: A4




PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	GLASS FILLED THERMOPLASTIC RATED. (UL94V-0)	1	COLOR : BROWN
2	SLIDER		1	COLOR : BLACK
3	CONTACT	PHOSPHOR BRONZE	n	PLATING : TIN Ni UNDER PLATED(LEAD FREE)




n : NO. OF CONTACTS

NOTES


1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
2. FLATNESS OF CONTACT TERMINAL MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING.
3. THIS DIMENSION IS SPACE FOR THE NOZZLE OF MOUNTER.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN.

RECOMMENDED PC BOARD LAYOUT (COMPONENT SIDE)



mat'l. code				surface 58 <input checked="" type="checkbox"/> tolerance ISO 1302 <input checked="" type="checkbox"/> ISO 406 <input checked="" type="checkbox"/> ISO 1101		projection 		product family 58SF				CODE JP		
ltr	ecn no	dr	date	tolerances unless otherwise specified				title 1mm SPACING SURFACE MOUNT FPC/FFC CONNECTOR (CAT.No.SFW__S-2ST__LF)						
A	J05-0377	H.T	6/22/05	angles	linear	±0.2								
B	J05-0731	H.T	10/28/05											
C	J06-0430	H.T	10/19/06			scale \times		dwg no sheet 1 of 1 size A4 JSA 96517						
				dr	<i>H. phillips</i>	10/19/06								
				enrg	<i>H. phillips</i>	10/19/06								
				chr	<i>R. S. House</i>	10/19/06								
				appd	<i>S. Duda</i>	10/20/06								
sheet index		revision sheet	C 1											Rev. c

SC-SFWS 03 JSA96516
form: A4




PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	GLASS FILLED THERMOPLASTIC RATED. (UL94V-0)	1	COLOR : BROWN
2	SLIDER		1	COLOR : BLACK
3	CONTACT	PHOSPHOR BRONZE	n	PLATING : TIN Ni UNDER PLATED(LEAD FREE)
4	MOUNTING PLATE	BRASS	2	

n : NO. OF CONTACTS

NOTES

1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND COPS WITH AUTOMATIC MOUNTING (SMT).
2. FLATNESS OF CONTACT TERMINAL AND MOUNTING PLATE MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING.
3. THIS DIMENSION IS SPACE FOR THE NOZZLE OF MOUNTER.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN.

RECOMMENDED PC BOARD LAYOUT (COMPONENT SIDE)



mat'l. code				surface 58	tolerance	projection	product family	58SF	CODE
				ISO 1302	ISO 406				JP
				tolerances unless otherwise specified					
ltr	ecn no	dr	date	angles	linear	mm	title		
A	J05-0377	H.T	6/22/05				1mm SPACING SURFACE MOUNT		
B	J05-0731	H.T	10/28/05				FPC/FFC CONNECTOR		
C	J06-0430	H.T	10/19/06				(CAT.No.SFW__S-2STM__LF)		
				dr	10/19/06	FCI	dwg no		sheet 1 of 1
				enr	10/19/06		JSA 96518		size
				chr	10/19/06				A4
				appd	10/20/06		type Product Customer Drawing		
sheet	revision	C							Rev.
index	sheet	1							C

SC-SFWS 03 JSA96516
form: A4

CAT. NO. & DIMENSIONS

(NOTE4)	NO. OF CONTACTS (n)	CAT. NO. (NOTE2)	DIMENSIONS (NOTE3)		
			D MAX.	E ± 0.3	F ± 0.1
	4	SFW4S-2ST_E9LF	30.4	24	—
	5	SFW5S-2ST_E9LF	30.4	24	—
	6	SFW6S-2ST_E9LF	30.4	24	—
*	7	SFW7S-2ST_E9LF	30.4	24	—
	8	SFW8S-2ST_E9LF	30.4	24	—
*	9	SFW9S-2ST_E9LF	30.4	24	—
	10	SFW10S-2ST_E9LF	30.4	24	—
	11	SFW11S-2ST_E9LF	30.4	24	—
*	12	SFW12S-2ST_E9LF	38.4	32	28.4
	13	SFW13S-2ST_E9LF	38.4	32	28.4
	14	SFW14S-2ST_E9LF	38.4	32	28.4
	15	SFW15S-2ST_E9LF	38.4	32	28.4
	16	SFW16S-2ST_E9LF	50.4	44	40.4
	17	SFW17S-2ST_E9LF	50.4	44	40.4
*	18	SFW18S-2ST_E9LF	50.4	44	40.4
*	19	SFW19S-2ST_E9LF	50.4	44	40.4
	20	SFW20S-2ST_E9LF	50.4	44	40.4
*	21	SFW21S-2ST_E9LF	50.4	44	40.4
	22	SFW22S-2ST_E9LF	50.4	44	40.4
	23	SFW23S-2ST_E9LF	50.4	44	40.4
	24	SFW24S-2ST_E9LF	50.4	44	40.4
*	25	SFW25S-2ST_E9LF	50.4	44	40.4
	26	SFW26S-2ST_E9LF	50.4	44	40.4
*	27	SFW27S-2ST_E9LF	62.4	56	52.4
	28	SFW28S-2ST_E9LF	62.4	56	52.4
	29	SFW29S-2ST_E9LF	62.4	56	52.4
	30	SFW30S-2ST_E9LF	62.4	56	52.4
*	31	SFW31S-2ST_E9LF	62.4	56	52.4
*	32	SFW32S-2ST_E9LF	62.4	56	52.4

CAT. NO. SFW (n) S - 2 ST_ _ _ LF

SERIES

NO. OF CONTACTS

STRAIGHT TYPE

FOR FPC / FFC

VARIATION

STM:FOR AUTOMATIC MOUNTING (SMT)
WITH MOUNTING PLATE

ST:FOR AUTOMATIC MOUNTING (SMT)
WITHOUT MOUNTING PLATE


PACKAGE STYLE

LEAD FREE


NOTES

1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND COTES WITH AUTOMATIC MOUNTING (SMT).
2. THIS CATALOG NO. INDICATES PLASTIC TAPE PACKAGED CONNECTOR.
3. SEE PART DRAWINGS FOR DIMENSIONS D~F.
4. PLEASE CONSULT US IN CASE OF USING PARTS WITH * MARK.

mat'l. code				surface 58/ tolerance ISO 1302 406 ISO 1101		projection		product family 58SF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title			
A	J09-0202	M.Y	2009-5-25	angles	linear	scale X		CAT NO. TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONN. (CAT.No.SFW__S-2ST_E9LF)			
				dr	H.YAMASHITA	2009-5-25	FCI		dwg no		sheet 1 of 1
				engr	H.YAMASHITA	2009-5-25			JSA 97526		size A4
				chr	S. Nishida	2009-5-25					
				appd	S. Nishida	2009-5-25					
sheet index		revision	A					type Product Customer Drawing		Rev. A	



DRAWING DIRECTION

END
PORTIONCONNECTOR PACKAGING
PORTION20 HOLES MIN.
(SPACE)

CONNECTOR PACKAGING STYLE

PT. NO.	PARTS NAME	CAT. NO.	MATERIAL	Q'TY	NOTE
1	REEL	_____	POLYSTYRENE	1	COLOR : WHITE or BLACK
2	PLASTIC (EMBOSSSED) TAPE	_____	PET	_____	COLOR : TRANSPARENCY
3	COVER	_____	POLYESTER	_____	COLOR : TRANSPARENCY
4	CONNECTOR	SFW__S-2ST_LF	SEE ATTACHED DWG.	500	_____

NOTES


- THIS IS PLASTIC TAPE PACKAGED CONNECTOR USED FOR FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
- SEE JIS C 0806 (PACKING OF ELECTRONIC COMPONENTS ON CONTINUOUS TAPES (SURFACE MOUNTING DEVICES)) FOR SHAPE AND DIMENSIONS OF PLASTIC (EMBOSSSED) TAPE AND REEL.
- F DIMENSION IS PORTION OF THE CORE.

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family	58SF	CODE JP
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (Cat. No. SFW__S-2ST_E9LF)		
A	J09-0202	M.Y	2009-5-25	angles	linear				
				±5°		scale	dwg no		
				dr	2009-5-25	FCI	sheet 1 of 1 size		
				engr	2009-5-25				
				chr	2009-5-25				
				appd	2009-5-25				
sheet index	revision	A					type Product Customer Drawing		
	sheet	1							
									Rev. A

SC-SFWS03 JSA97525 97526
form: A4

RECOMMENDED CABLE (FPC)

n : NO. OF CONDUCTORS



PT. NO.	DESCRIPTION	MATERIAL	THICKNESS (μm)
1	BASE FILM	POLYIMIDE OR POLYESTER OR EQUIVALENT	25
2	CONDUCTOR	COPPER FOIL(PLATING : SOLDER $1\mu\text{m}$ MIN.)	35
3	OVERLAY	POLYIMIDE OR POLYESTER OR EQUIVALENT	—
4	SUPPORTING TAPE	POLYESTER OR POLYIMIDE OR EQUIVALENT	188


NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. TOTAL THICKNESS LIMIT OF EACH MATERIAL (INCLUDING ADHESIVE AGENT) IS SPECIFIED.

mat'l. code				surface 58 / tolerance ISO 406 / ISO 1101		projection		product family 58SF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title			
AA	J04-0333	H.T	Oct.13,'04					RECOMMENDED CABLE			
AB	J06-0430	H.T	10/19/06					(CAT.No.SFW__S-2ST__)			
				angles linear		scale X		dwg no sheet 1 of 1 size			
						FCI		JSA 93340 A4			
				dr 10/19/06				type Product Customer Drawing			
				enr 10/19/06							
				chr 10/19/06							
				appd 10/20/06							
sheet index	revision sheet	AB	1					Rev. AB			

RECOMMENDED CABLE (FFC)

n : NO. OF CONDUCTORS



PT. NO.	DESCRIPTION	MATERIAL	NOTE
1	INSULATOR	FLAME RESISTING POLYESTER OR EQUIVALENT	_____
2	CONDUCTOR	COPPER FOIL	PLATING: TIN OR SOLDER 1μm MIN.
3	SUPPORTING TAPE	FLAME RESISTING POLYESTER OR EQUIVALENT	_____

NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.

mat'l. code				surface 5B / tolerance ISO 406 / ISO 1302 ✓ / ISO 1101		projection		product family 58SF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified				title			
AA	J04-0333	H.T	06/13/04			mm		RECOMMENDED CABLE			
AB	J06-0430	H.T	10/19/06	angles	linear			(CAT.No.SFW__S-2ST__)			
				dr	10/19/06		dwg no		sheet 1 of 1		size
				enr	10/19/06		JSA 93341				A4
				chr	10/19/06		type		Product Customer Drawing		
				appd	10/20/06						
sheet index	revision	AB	1							Rev. AB	

form: A4

1

2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[SFW10S-2STE9LF](#) [SFW16S-2STE9LF](#) [SFW20S-2STE9LF](#) [SFW24S-2STE9LF](#) [SFW28S-2STE9LF](#) [SFW30S-2STE9LF](#) [SFW4S-2STE9LF](#) [SFW8S-2STE9LF](#)