



DIMENSIONS



P.C.B LAYOUT




CONTACT ARRANGEMENT

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32
a	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
b	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
c	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X

☒ STANDARD CONTACT ☐ EMPTY CAVITY ☒ FMLB CONTACT ☐ LMEB CONTACT

GENERAL CHARACTERISTICS & RoHS INFO
REFER DRAWING C-8609-0000A

TERMINATION



ORDERING INFORMATION

SERIES	8609	3	51	8	1	14	7	5	0	TELF
ROWS FITTED WITH CONTACTS										
ROW a b c		3	51							
NO. OF CONTACTS										
TYPE OF INSULATOR										
3 ROW FEMALE INSULATOR						8				
METHOD OF MOUNTING										
STANDARD MOUNTING - STYLE C							1			
TERMINATION										
LONG STRAIGHT SPILL (L=SEE TABLE)							14			
OPTIONS										
NO OPTION								7		
PERFORMANCE CLASS										
DIN 41612 CLASS 3									4	
DIN 41612 CLASS 2									5	
DIN 41612 CLASS 1									6	
AS PER MIL C 55302 / JSS 50808									8	
PITCH PER ROW										
MIXED PITCH									0	
LEAD FREE VERSION SPL CONTACTS LOADING										TELF

mat'l. code	surface	tolerance	projection	product family
-	ISO 1302	ISO 406 ISO 1101		8609
ltr	ecn no	dr	date	title
A	109-0064	JS	25/05/2009	DIN STANDARD RECEPTACLE
				STRAIGHT DIN 41612 STYLE-C
				dwg no
				sheet 1 of 1
				size
				A3
				type
				Product Customer Drawing
sheet index	revision sheet	A	1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86093518114750TELF](#)