





SIZE	Part Num.	Threading	Headscrew	Packaging(see notes1&2)
25	8655MHRA2501LF	UNC 4.40	Black	BULK (see note 1)
	8655MHRA2501KLF	UNC 4.40	Black	KIT (see note 2)
	8655MHRA2502LF	M3	Grey	BULK
	8655MHRA2502KLF	M3	Grey	KIT



1 KIT
SEE NOTE 2



DESIGNATION	REP.	09	15	25	37	50
COVER BOTTOM	1			1		
JACKSCREW	2	1		2		
STRAIN RELIEF	3			2		
COVER TOP	4			1		
SCREW POZIDRIVE	5			2		

Rev	ecn no	dr	date
H	F11-0046	APA	2011/04/05
J	F11-0073	APA	2011/06/17
D	F09-0223	LSA	2009/11/24
E	F09-0236	LSA	2009/12/22
F	F10-0093	APA	2010/08/31
G	F10-0213	LSA	2010/19/15

NOTES:

Material and finish: Zinc die-cast
Nickel plated

Cable strain relief: Polycarbonate (UL94V-0)

Jackscrews:

- Headscrew : plastic, colour according threading
- Body : metal, threading according tables

Temperature range: -40°C to 120°C
Cable diameter: 4.0 to 13.0mm
Attenuation factor: >40 dB between 30MHz and 1 GHz
Marking FCI logo: Height 6 mm for all versions

Covers screwing force (max): 100 Ncm
Jackscrew screwing force (max): 75 Ncm

Packaging notes (see tables):



- 1 - Bulk : Every spare part packaged per 100 or 200 into plastic bag. 5 plastic bags per carton box. 1 plastic bag per part.
- 2 - Kit : 1 set of spare parts necessary to realise 1 kit into a plastic bag. 100 plastic bags per carton box.

NOTE:RoHS INFORMATIONS



- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

www.fciconnect.com				surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
				ANGULAR	LINEAR	size	Scale
				0° ±/°	0.X ±/	A3	3:2
				0.XXX ±/	ECN	F11-0073	
				Product family	D-Sub	Spec ref	
				Title			
				D-SUB METAL SHELLS			
				ANGLED			
				catalog no			
				CUSTOMER			
				sheet 1 of 3			



SIZE	Part Num.	Threading	Headscrew	Packaging
09	8655MHRA0901LF	UNC 4.40	Black	BULK (see note 1)
	8655MHRA0901KLF	UNC 4.40	Black	KIT (see note 2)
	8655MHRA0902LF	M3	Grey	BULK
	8655MHRA0902KLF	M3	Grey	KIT





SIZE	Part Num.	Threading	Headscrew	Packaging
15	8655MHRA1501LF	UNC 4.40	Black	BULK (see note 1)
	8655MHRA1501KLF	UNC 4.40	Black	KIT (see note 2)
	8655MHRA1502LF	M3	Grey	BULK
	8655MHRA1502KLF	M3	Grey	KIT



SIZE	Part Num.	Threading	Headscrew	Packaging
37	8655MHRA3701LF	UNC 4.40	Black	BULK (see note 1)
	8655MHRA3701KLF	UNC 4.40	Black	KIT (see note 2)
	8655MHRA3702LF	M3	Grey	BULK
	8655MHRA3702KLF	M3	Grey	KIT



SIZE	Part Num.	Threading	Headscrew	Packaging
50	8655MHRA5001LF	UNC 4.40	Black	BULK (see note 1)
	8655MHRA5001KLF	UNC 4.40	Black	KIT (see note 2)
	8655MHRA5002LF	M3	Grey	BULK
	8655MHRA5002KLF	M3	Grey	KIT




www.fciconnect.com			surface ISO 1302	✓	tolerance std ISO 406	ISO 1101	projection ⊕	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED				size A3	Scale 1:1
Dr	BART.S	2005/10/15	ANGULAR	LINEAR	0.X	±/		
Eng	LENOIR.M	2005/10/15			0.XX	±/		
Chr	LEGARE.P	2005/10/15	0° ±/°		0.XXX	±/		
Appr	LEGARE.P	2005/10/15	Product family D-Sub				Spec ref	
FCI			Title D-SUB METAL SHELLS			dwg no 10061512C		Rev. J
			ANGLED			CUSTOMER		sheet 2 of 3
			catalog no					


REV C - 2006-03-28

CABLING INSTRUCTIONS


- 1- Use two halves of strain relief, different sizes can be mixed ($\varnothing 4, 5, 7$ or 9)




- 2- Strip cable 18mm and shape to two pigtails




- 3- Attach the strain relief around the cable




- 4- Bend cable shielding back on outside of strain relief



- 5- Mount connector and cable into the backshell



- 6- Assemble the other half screwing force: 100 Ncm



Copyright FCI.

www.fciconnect.com			Surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 	mm 
			TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	BART.S	2005/10/15	ANGULAR	LINEAR	0.X	±/	size	Scale	
Eng	LENOIR.M	2005/10/15			0.XX	±/	A3	3:2	
Chr	LEGARE.P	2005/10/15			0° ±/°	0.XXX	±/	ECN	F11-0073
Appr	LEGARE.P	2005/10/15	Product family D-Sub				Spec ref		
	title D-SUB METAL SHELLS					dwg no 10061512C		Rev	
	ANGLED							J	
	catalog no					CUSTOMER		sheet 3 of 3	

REV C - 2006-03-28

PDM: Rev:J

STATUS:Released

Printed: Aug 20, 2011

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8655MHRA1501KLF](#) [8655MHRA3701KLF](#) [8655MHRA1502KLF](#) [8655MHRA0902LF](#) [8655MHRA3702KLF](#)
[8655MHRA2502KLF](#) [8655MHRA5002KLF](#) [8655MHRA5001KLF](#) [8655MHRA0901KLF](#) [8655MHRA1502LF](#)
[8655MHRA3702LF](#) [8655MHRA0902KLF](#) [8655MHRA5002LF](#) [8655MHRA2502LF](#)