








.062

VIEW AT N
10SL ONLY


STAMP "AMPHENOL", DATE CODE 
(9-3895) & MS NO. PER 9-2811
EXAMPLE:

AMPHENOL-7539 JMS3106R-10
OR
STAMP "AMPHENOL" & SM NO.
PER 9-2811
EXAMPLE:
AMPHENOL SM3106R-10SL-3S
NUT MUST TURN FREELY
AFTER STAMPING



.063

STAMP MS NO. 4 13
"AMPHENOL" & DATE
CODE(9-3895) OPPOSITE KEYWAY PER 9-2811
EXAMPLE:
JMS3106R-8S-1S AMPHENOL-7539
OR
STAMP SM NO. 4 14
OPPOSITE KEYWAY
PER 9-2811
EXAMPLE:
MSL SM3106R-8S-1S



CONTACT DATA (WHERE APPLICABLE)			
THERMOCOUPLE		COAXIAL	
MATERIAL	IDENTIFICATION	ARR	CABLE
CHROMEL	WHITE		
ALUMEL	GREEN		
IRON	BLACK		
CONSTANTAN	YELLOW		
INSERT ARRANGEMENTS CONTAINING THERMOCOUPLE OR COAXIAL CONTACTS MUST HAVE SUCH CONTACTS ASSEMBLED INTO THE INSERT IN PROPER LOCATIONS AS SPECIFIED BY APPLICABLE DRAWING L-11908-() THRU L-11948-().			

STANDARD SOLDER WELL DATA						SPECIAL SOLDER WELL DATA			THERMOCOUPLE	
CONTACT SIZE	0	4	8	12	16	8 FOR NO. 6 WIRE	12 FOR NO. 10 WIRE	16 FOR NO. 12 WIRE	12	16
WELL DIA	.469 ⁺ .005 -.003	.332 ⁺ .005 -.003	.209 ⁺ .004 -.002	.116 ⁺ .004 -.002	.078 ⁺ .004 -.002	.250±.003	.152 ⁺ .004 -.002	.109 ⁺ .004 -.001	.125 ⁺ .004 -.002	.094 ⁺ .004 -.002
WELL DEPTH +.031 -.000	.625	.625	.500	.375	.250	.500	.250	.188	.250	.188

FIND NO.	QTY REQD	CODE IDENT	PART NUMBER	DESCRIPTION	NOTE REF
PARTS LIST					
UNLESS OTHERWISE SPECIFIED LINEAR DIMENSIONS ARE IN INCHES. TOLERANCES: .XXX ± .010, .XX ± .03, .X ± .1, ANGLES ± 2°. OTHER STANDARDS PER 9-3800 AND MIL-D-1000. NOTE REF			SIGNATURES	DATES	The Bendix Corporation Electrical Components Division Sidney, New York TITLE: CONNECTOR, ELECTRICAL PLUG, TYPE MS-R, SM-R OMC.
MATERIAL SPEC PROCESS SPEC TEST 9-3106-5 ASSY 9-3103-1 ----- 9-2437 9-2811 9-3895			PREPARED E PESSAGNO	1-7-66	
			CHECKED <i>[Signature]</i>	10-2-73	
			MATERIAL		
			APPROVED <i>E. Chaplin</i>	12-7-72	
			APPROVED <i>J.M. [Signature]</i>	10-4-73	

4		3		2		1											
ASSEMBLY NUMBER	13 14 MS OR SM NO.	SHELL SIZE	SHELL	COUPLING NUT	SLEEVE	NUT	SCREW (2 REQ'D)	PACKING	A MAX	B THREAD CLASS 2B	C +.047 -.000	D MAX	F MAX	G THREAD CLASS 2	H ±.005	J DIA MAX	L DIA MAX
10-190608-	3106R-8S-	-8S	10-37266- 8	10-37265- 8	10-130029-83	10-130028- 83	10-101152-- 83	10-101937-08	.607	.500 -28UNEF	.531	1.057	.959	6-32UNC	.531	.741	.557
10-190610-	-10S-	-10S	10-37266-10	10-37265-10	-103	-103	10-101152-83	10-101937-10		.625 -24UNEF			1.026			.875	.682
10-190611-	-10SL-	-10SL	10-113488-11	(SHELL ASSY)	-123	-123		10-101937-10		.625 -24UNEF			1.120			.946	.807
10-190612-	-12S-	-12S	10-37266-12	10-37265-12	-123	-123		10-101937-12		.750 -20UNEF			1.120			.995	.807
10-190613-	-12-	-12	-13	-13	-123	-133		10-101937-12	.857	.750 -20UNEF	.719	1.212	1.120		.719	.995	.807
10-190614-	-14S-	-14S	-14	-14	-143	-143		10-101937-14	.607	.875 -20UNEF	.531	1.057	1.307		.531	1.123	.932
10-190615-	-14-	-14	-15	-15	-143	-153		10-101937-14	.857	.875 -20UNEF	.719	1.212	1.307		.719	1.123	.932
10-190616-	-16S-	-16S	-16	-16	-163	-163		10-101937-16	.607	1.000 -20UNEF	.531	1.057	1.432		.531	1.250	1.057
10-190617-	-16-	-16	-17	-17	-163	-173		10-101937-16	.857	1.000 -20UNEF	.719	1.212	1.432		.719	1.250	1.057
10-190618-	-18-	-18	-18	-18	-183	-183		10-101937-18		1.125 -18UNEF			1.557			1.333	1.182
10-190620-	-20-	-20	-20	-20	-203	-203	10-101151-83	10-101937-20		1.250 -18UNEF			1.744	8-32UNC		1.461	1.291
10-190622-	-22-	-22	-22	-22	-223	-223	10-101151-83	10-101937-22		1.375 -18UNEF			1.869	8-32UNC		1.588	1.432
10-190624-	-24-	-24	-24	-24	-243	-243	10-101151-93	10-101937-24		1.500 -18UNEF		1.291	1.994			1.715	1.557
10-190628-	-28-	-28	-28	-28	-283	-283	10-101151-93	10-101937-28		1.750 -18UNS			2.166			1.968	1.807
10-190632-	-32-	-32	-32	-32	-323	-323	10-101270-93	10-101937-32		2.000 -18UNS		1.353	2.541	10-32UNF		2.209	2.057
10-190636-	-36-	-36	-36	-36	-363	-363		10-101937-36		2.250 -16UN			2.729			2.463	2.260
10-190640-	-40-	-40	-40	-40	-403	-403		10-101937-40		2.500 -16UN			2.979			2.719	2.510
10-190641/50-			NOT AVAILABLE														

- FOR COMPONENT PART NUMBERS, QUANTITIES AND RELEASE STATUS OF THE DESIRED UNIT, SEE SEPARATE PARTS LIST.
- FOR CONTACT SIZE, SPACING & SERVICE RATING SEE DRAWINGS MS33680 THRU MS33693 & L-11908/48.
- DIMENSION INDICATES FINAL INSTALLATION. FOR STORAGE & SHIPPING, NUT & SLEEVE MUST BE LOOSELY COUPLED.
- SEE WORK ORDER FOR PERMISSIBLE ADDITIONAL OR ALTERNATE STAMPING.
- TO COMPLETE ASSY NO., MS NO., OR SM NO., ADD APPLICABLE INSERT ARRANGEMENT SUFFIX TO BASE NUMBERS LISTED ABOVE (FOR ALTERNATE ARRANGEMENTS, REFER TO 9-2437).
- SEE DRAWING 10-190208 THRU 10-190250 & OTHERS FOR MATING RECEPTACLE ASSEMBLIES.
- LUBRICATE PACKING WITH A THIN COATING OF COMPOUND MIL-S-8660.
- ALL LOCKWIRE HOLES ARE .045 DIA MIN.

- UNITS ILLUSTRATED MEET THE MATERIAL & FINISH REQUIREMENTS OF MIL-C-5015.
- ALL UNUSED GROMMET HOLES MUST BE FILLED WITH APPROPRIATE SIZE SEALING PLUGS. SEALING PLUGS ARE PART OF MS STAMPED ASSEMBLIES ONLY.
- PACKAGE PER PRODUCTION PROCESS SHEET.
- INCREASE "A" DIMENSION BY .312 FOR SIZE "O" CONTACT ONLY.
- CONNECTOR ASSEMBLIES 10-190608-1/-49 THRU 10-190650-1/-49 AND 10-190636-52, 10-190640-56 AND 10-190640-62 ARE STAMPED WITH MS NO.
- CONNECTOR ASSEMBLIES 10-190608-50/ 10-190650-50/-99, EXCEPT THOSE LISTED IN NOTE 13, ARE STAMPED WITH SM NO.

NOTES:

SIZE	CODE IDENT NO.	10-190608 THRU 10-190650
C	77820	
SCALE	REF	SHEET 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MS3106R10SL-3S](#) [MS3106R10SL-4S](#) [MS3106R14S-2S](#) [MS3106R14S-5P](#) [MS3106R14S-5S](#) [MS3106R14S-6P](#)
[MS3106R14S-6S](#) [MS3106R14S-7S](#) [MS3106R16-11S](#) [MS3106R16S-1S](#) [MS3106R16S-8P](#) [MS3106R18-11S](#)
[MS3106R20-27P](#) [MS3106R22-14P](#) [MS3106R22-14S](#) [MS3106R24-11S](#) [MS3106R28-21S](#) [MS3106R20-15S](#)
[MS3106R10SL-3P](#) [MS3106R12S-3S](#) [MS3106R20-27S](#) [MS3106R20-29S](#) [MS3106R20-29P](#) [MS3106R18-1S](#)
[MS3106R18-1P](#) [MS3106R18-4S](#) [MS3106R18-4P](#) [MS3106R18-11P](#) [MS3106R14S-2P](#) [MS3106R14S-7P](#)
[MS3106R16-10P](#) [MS3106R24-9P](#) [MS3106R16S-8S](#) [MS3106R20-23P](#) [MS3106R24-9S](#) [MS3106R22-23P](#)
[MS3106R12-5S](#) [MS3106R18-13P](#) [MS3106R20-15P](#) [MS3106R20-24S](#) [MS3106R32-17S](#) [MS3106R16-10SX](#)
[MS3106R20-22SW](#) [MS3106R22-22PY](#) [MS3106R28-10SW](#) [MS3106R28-21SW](#) [MS3106R32-17SW](#) [MS3106R16-](#)
[10PW](#) [MS3106R16-10PX](#) [MS3106R16-11P](#) [MS3106R16-10S](#) [MS3106R24-11P](#) [MS3106R20-7S](#) [MS3106R20-7P](#)
[MS3106R20-4S](#) [MS3106R20-4P](#) [MS3106R24-28P](#) [MS3106R24-28S](#) [MS3106R16S-1P](#) [MS3106R28-21P](#)
[MS3106R22-7S](#) [MS3106R18-9P](#) [MS3106R20-18S](#) [MS3106R22-2S](#) [MS3106R18-9S](#) [MS3106R14S-2SX](#)
[MS3106R24-10S](#) [MS3106R22-23S](#) [MS3106R22-19S](#) [MS3106R18-19S](#) [MS3106R22-2P](#) [MS3106R22-22S](#)
[MS3106R22-22P](#) [MS3106R12-5P](#) [MS3106R16-9P](#) [MS3106R16-9S](#) [MS3106R16S-5P](#) [MS3106R16S-5S](#)
[MS3106R18-15S](#) [MS3106R18-19P](#) [MS3106R18-3P](#) [MS3106R18-3S](#) [MS3106R20-14P](#) [MS3106R20-14S](#)
[MS3106R20-16S](#) [MS3106R20-18P](#) [MS3106R20-22P](#) [MS3106R20-22S](#) [MS3106R22-10P](#) [MS3106R22-18S](#)
[MS3106R22-27S](#) [MS3106R22-7P](#) [MS3106R24-12P](#) [MS3106R24-12S](#) [MS3106R28-10P](#) [MS3106R28-10S](#)
[MS3106R28-12P](#) [MS3106R28-12S](#) [MS3106R28-9P](#) [MS3106R32-1P](#)